




**Part Number :** [190670096](#)  
**Product Description :** NylaKrimp Funnel Entry  
Ring Tongue Terminal for 2 AWG Wire, Stud  
Size 1/4" (M6)  
**Series Number :** 19067  
**Status :** Active  
**Product Category :** Ring and Spade Terminals  
**Engineering Number :** G-975-14



## Documents & Resources

### Drawings

[Drawing 190670096\\_sd.pdf](#)

### 3D Models and Design Files

[3D Model 190670096\\_stp.zip](#)

### Specifications

[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-013-001.pdf](#)

[Product Specification PS-19902-016-001.pdf](#)

## Product Environment Compliance

### Compliance

|                    |                                                |
|--------------------|------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                   |
| China RoHS         | Not Relevant                                   |
| EU ELV             | Not Relevant                                   |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                 |
| REACH SVHC         | Not Contained per D(2023)3788-DC (14 Jun 2023) |
| EU RoHS            | Compliant per EU 2015/863                      |

### [Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

## Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

|                |                                                                                       |
|----------------|---------------------------------------------------------------------------------------|
| Status         | Active                                                                                |
| Category       | Ring and Spade Terminals                                                              |
| Series         | 19067                                                                                 |
| Description    | NylaKrimp Funnel Entry Ring<br>Tongue Terminal for 2 AWG Wire,<br>Stud Size 1/4" (M6) |
| Keyword        | Ring Terminal, Ring Terminals                                                         |
| Product Family | Solderless Terminals                                                                  |
| Product Name   | NylaKrimp                                                                             |
| Type           | Ring                                                                                  |
| UPC            | 800753066762                                                                          |

#### Agency

|     |         |
|-----|---------|
| CSA | LR18689 |
| UL  | E32244  |

#### Physical

|                           |                 |
|---------------------------|-----------------|
| Barrel Type               | Closed - Brazed |
| Flammability              | 94V-2           |
| Insulation                | Nylon (PA)      |
| Material - Plating Mating | Tin             |
| Net Weight                | 15.704/g        |
| Packaging Type            | Bag             |
| Plating min - Mating      | 2.540µm         |
| Plating min - Termination | 2.540µm         |
| Stud Size                 | 1/4" (M6)       |

|                             |                      |
|-----------------------------|----------------------|
| Termination Interface Style | Crimp or Compression |
| Wire Insulation Diameter    | 15.24mm max.         |
| Wire Size (AWG)             | 2                    |

---

## Application Tooling

### Global

| Description                                         | Part Number       |
|-----------------------------------------------------|-------------------|
| Manual Putt Pump Hydraulic System, Die set required | <u>0192860117</u> |
| Die Set (Large) for the HHLS Hydraulic Crimper      | <u>0192890010</u> |
| Hydraulic Dieless Crimping Tool                     | <u>0638161700</u> |
| PremiumGrade Hand Crimp Tool for 2-8 AWG Terminals  | <u>0640013900</u> |
| Hand Crimp Tool for 2 AWG Insulated Ring Terminals  | <u>0640017970</u> |