



Part Number : [192210245](#)


Product Description : Compression Style Ring Tongue Terminal for 2/0 AWG Wire, Stud Size 1/2" (M12), Plated

Series Number : 19221

Status : Active

Product Category : Ring and Spade Terminals

Engineering Number : BCL-2012-PL



Documents & Resources

Drawings

[Drawing 192210245_sd.pdf](#)

3D Models and Design Files

[3D Model 192210245_stp.zip](#)

Specifications

[Product Specification PS-19902-017-001.pdf](#)


[Product Specification PS-19902-013-001.pdf](#)

[Product Specification PS-19901-017-001.pdf](#)

[Product Specification PS-19902-011-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS

- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19221
Description	Compression Style Ring Tongue Terminal for 2/0 AWG Wire, Stud Size 1/2" (M12), Plated
Comments	Heavy Duty
Keyword	Ring Terminal, Ring Terminals
Product Family	Battery Cable Lugs
Product Name	Battery Cable Lug
Type	Ring
UPC	800753062443

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	20.285/g
Packaging Type	Bag
Plating min - Mating	4.064µm
Plating min - Termination	4.064µm

Stud Size	1/2" (M12)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	N/A
Wire Size (AWG)	2/0

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for Eyelet Style Copper Lug Terminals 8-4/0 AWG	<u>0192840034</u>
Manual Putt Pump Hydraulic System, Die set required	<u>0192860117</u>
Die Set (Large) for the HHLS Hydraulic Crimper	<u>0192900012</u>
Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	<u>0192940008</u>
Hydraulic Dieless Crimping Tool	<u>0638161700</u>
Square "Din" Style Die Set for BCL and VersaKrimp Un-insulated Ring Tongue Terminals and Splices, 1/0 and 2/0 AWG	<u>0640038070</u>