



Part Number : [1600740001](#)

Product Description : MX150 Mat-Sealed Female Connector Assembly, Dual Row, 20 Circuits, UL 94V-0, Keying Option A, without Connector Position Assurance, Black

Series Number : 160074

Status : Active

Product Category : Connector Housings



Documents & Resources

Drawings

[Drawing 1600740001_sd.pdf](#)

[Packaging Design Drawing PK-31300-635-001.pdf](#)

3D Models and Design Files

[3D Model 1600740001_stp.zip](#)

Specifications

[Application Specification AS-33472-100-001.pdf](#)

[Application Specification AS-33472-100-CH-001.pdf](#)

[Application Specification AS-33472-100-FR-001.pdf](#)

[Product Specification PS-160074-0001-001.pdf](#)

[Test Summary 1600742276-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Duty-To-Declare
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	160074
Description	MX150 Mat-Sealed Female Connector Assembly, Dual Row, 20 Circuits, UL 94V-0, Keying Option A, without Connector Position Assurance, Black
Application	Power, Wire-to-Board, Wire-to-Wire
Product Family	MX150 Sealed and Unsealed Connector System
Product Name	MX150
UPC	889056421393

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	20
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	26.135/g
Number of Rows	2

Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarization	A
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Use with Part(s)

Description	Part Number
MX150 Sealed Receptacle Cavity Plug	/content/molex/molex-dot-com/us/en/products/product-page.html/343454001.html
MX150 Female Terminals	<u>33001</u>
MX150 Female Terminals	<u>33012</u>
