



Part Number : [2127242021](#)
Product Description : Micro-One Wire-to-Board Receptacle Housing, 2.00mm Pitch, Single Row, Glow-Wire Capable, 2 Circuits
Series Number : 212724
Status : Active
Product Category : Connector Housings



Documents & Resources

Drawings

[Drawing 2127242021_sd.pdf](#)

3D Models and Design Files

[2D Drawing DXF 2127242021.dxf](#)
[2D Drawing DXF \(PDF\) 2127242021.pdf](#)
[3D Model 2127242021_stp.zip](#)

Specifications

[Application Specification 2059790000-AS-000.pdf](#)
[Packaging Specification 2127249200-SPK-200.pdf](#)
[Product Specification 2059790000-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	212724
Description	Micro-One Wire-to-Board Receptacle Housing, 2.00mm Pitch, Single Row, Glow-Wire Capable, 2 Circuits
Application	Signal, Wire-to-Board
Product Family	Micro-One Wire-to-Board Connector System
Product Name	Micro-One
UPC	193264613472

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	2
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyamide
Net Weight	191.270/mg
Number of Rows	1
Packaging Type	Bag

Panel Mount	No
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	No
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Micro-One Vertical Single Row Headers	<u>205971</u>
Micro-One Vertical Single Row Headers	<u>217063</u>
Micro-One Right-Angle Single Row Headers	<u>205972</u>
Micro-One Right-Angle Single Row Headers	<u>217064</u>
Micro-One Vertical, Single Row, Through Hole Headers	<u>220029</u>
Micro-One Right-Angle, Single Row, Through Hole Headers	<u>220030</u>

Use with Part(s)

Description	Part Number
2.00mm Pitch Crimp Terminal, Female, 22-24 AWG, Reel	<u>/content/molex/molex-dot-com/us/en/products/product-page.html/561349001.html</u>
2.00mm Pitch Crimp Terminal, Female, 26-28 AWG, Reel	<u>/content/molex/molex-dot-com/us/en/products/product-page.html/561349002.html</u>
Micro-One Terminal Position Assurance (TPA) Retainers	<u>212725</u>