



**Part Number :** [2127242031](#)  
**Product Description :** Micro-One Wire-to-Board Receptacle Housing, 2.00mm Pitch, Single Row, Glow-Wire Capable, 3 Circuits  
**Series Number :** 212724  
**Status :** Active  
**Product Category :** Connector Housings



## Documents & Resources

### Drawings

[Drawing 2127242031\\_sd.pdf](#)

### 3D Models and Design Files

- [2D Drawing DXF 2127242031.dxf](#)
- [2D Drawing DXF \(PDF\) 2127242031.pdf](#)
- [3D Model 2127242031\\_stp.zip](#)

### Specifications

- [Application Specification 2059790000-AS-000.pdf](#)
- [Packaging Specification 2127249200-SPK-200.pdf](#)
- [Product Specification 2059790000-PS-000.pdf](#)

## Product Environment Compliance

### Compliance

|                    |                                                |
|--------------------|------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                   |
| China RoHS         |                                                |
| EU ELV             | Not Relevant                                   |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21             |
| REACH SVHC         | Not Contained per D(2023)3788-DC (14 Jun 2023) |
| EU RoHS            | Compliant per EU 2015/863                      |

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

## Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

|                |                                                                                                     |
|----------------|-----------------------------------------------------------------------------------------------------|
| Status         | Active                                                                                              |
| Category       | Connector Housings                                                                                  |
| Series         | 212724                                                                                              |
| Description    | Micro-One Wire-to-Board Receptacle Housing, 2.00mm Pitch, Single Row, Glow-Wire Capable, 3 Circuits |
| Application    | Signal, Wire-to-Board                                                                               |
| Product Family | Micro-One Wire-to-Board Connector System                                                            |
| Product Name   | Micro-One                                                                                           |
| UPC            | 193264613496                                                                                        |

#### Agency

|    |        |
|----|--------|
| UL | E29179 |
|----|--------|

#### Physical

|                       |            |
|-----------------------|------------|
| Circuits (maximum)    | 3          |
| Color - Resin         | Black      |
| Gender                | Receptacle |
| Glow-Wire Capable     | Yes        |
| Keying to Mating Part | None       |
| Lock to Mating Part   | Yes        |
| Material - Resin      | Polyamide  |
| Net Weight            | 258.310/mg |
| Number of Rows        | 1          |
| Packaging Type        | Bag        |

|                               |                |
|-------------------------------|----------------|
| Panel Mount                   | No             |
| Pitch - Mating Interface      | 2.00mm         |
| Polarized to Mating Part      | No             |
| Stackable                     | No             |
| Temperature Range - Operating | -40° to +105°C |

---

## Mates With / Use With

### Mates with Part(s)

| Description                                             | Part Number                   |
|---------------------------------------------------------|-------------------------------|
| Micro-One Vertical Single Row Headers                   | <u><a href="#">205971</a></u> |
| Micro-One Vertical Single Row Headers                   | <u><a href="#">217063</a></u> |
| Micro-One Right-Angle Single Row Headers                | <u><a href="#">205972</a></u> |
| Micro-One Right-Angle Single Row Headers                | <u><a href="#">217064</a></u> |
| Micro-One Vertical, Single Row, Through Hole Headers    | <u><a href="#">220029</a></u> |
| Micro-One Right-Angle, Single Row, Through Hole Headers | <u><a href="#">220030</a></u> |

### Use with Part(s)

| Description                                           | Part Number                                                                                                                                                                    |
|-------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 2.00mm Pitch Crimp Terminal, Female, 22-24 AWG, Reel  | <u><a href="/content/molex/molex-dot-com/us/en/products/product-page.html/561349001.html">/content/molex/molex-dot-com/us/en/products/product-page.html/561349001.html</a></u> |
| 2.00mm Pitch Crimp Terminal, Female, 26-28 AWG, Reel  | <u><a href="/content/molex/molex-dot-com/us/en/products/product-page.html/561349002.html">/content/molex/molex-dot-com/us/en/products/product-page.html/561349002.html</a></u> |
| Micro-One Terminal Position Assurance (TPA) Retainers | <u><a href="#">212725</a></u>                                                                                                                                                  |