




Part Number : [1731120669](#)
Product Description : FCT High Power Contact, Female, Straight, Crimp, 1.30µm Gold Mating Plating, 0.20µm Gold Termination Plating, Split Tine, 20.0A, 12-14 AWG
Series Number : 173112
Status : Active
Product Category : D-Sub Contacts
Engineering Number : FMP003S110



Documents & Resources

Drawings
[Drawing 1731120669_sd.pdf](#)

Specifications
[Application Specification 2195600660-000.pdf](#)
[Packaging Specification 1731120008-PK-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	D-Sub Contacts
Series	173112
Description	FCT High Power Contact, Female, Straight, Crimp, 1.30µm Gold Mating Plating, 0.20µm Gold Termination Plating, Split Tine, 20.0A, 12-14 AWG
Contact Type	High Power
Product Family	FCT D-Sub Connectors
Product Name	FCT Products
Type	Mixed Layout
UPC	191128757263

Electrical

Current - Maximum per Contact	20.0A
-------------------------------	-------

Physical

Durability (mating cycles max)	500
Gender	Female
Material - Contact	Copper Alloy
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Gold over Nickel
Material - Retaining Clip	Copper Alloy
Net Weight	1.900/g
Orientation	Straight
Packaging Type	Bag
Plating min - Mating	1.300µm

Plating min - Termination	0.200µm
Temperature Range - Operating	-55° to +155°C
Termination Style	Crimp
Wire Size (AWG)	12, 14

Use with Part(s)

Description	Part Number
Use With	FCT Mixed Layout Connectors

Application Tooling

Global

Description	Part Number
FCT Hand Crimp Tool, 8-Step Adjust	<u>1731121731</u>
FCT Locator for High Power Contacts	<u>1731121734</u>
FCT Removal Tool for Size 8 Contacts	<u>1731121747</u>