



Aluminum Height-Adjustable Multimedia TV Cart

Holds One 37" to 86" TV up to 50 kg (110 lbs.), -10 to 5° Tilt, 90° Rotation, Shelf for Laptop or AV Device, Silver/Black

Part No.: **462327**

EAN-13: 0766623462327 | UPC: 766623462327

Premium Multimedia Rolling TV Stand that lets you wheel your display where you want it

Bring the TV to you. When it needs to be somewhere else, move it there with ease. The Manhattan Aluminum Height-Adjustable Multimedia TV Cart puts the TV on wheels so you can take it to different spaces as needed, avoid an annoying glare, or overcome a restrictive furniture setup. VESA-compliant and constructed of quality aluminum materials, this well-made, heavy-duty rolling TV stand supports TVs up to 86" and can support a total weight up to 50 kg (110 lbs.).

The Premium Multimedia TV Trolley has all the benefits of the above-the-floor wall-mount installation — elevated views, a more professional look, greater security for your TV, etc. — plus mobile flexibility and independence. It includes an AV shelf to hold and connect a laptop, Blu-ray player or streaming device, so most everything you need can be on-board, connected and ready to go when you get to your new destination. You'll get there swiftly and smoothly with the heavy-duty steel casters that have treaded polyurethane wheels to absorb bumps along the way.

This Heavy-duty TV stand on wheels is ideal for residential, office, hospitality, classroom and conference room, and other commercial purposes. It's an excellent choice in digital signage applications since it lets you rotate the display from landscape to portrait orientation and vice-versa, depending on your needs.

Features:

- Multifunctional TV cart/trolley for one 37" to 86" TV up to 50 kg (110 lbs.)
- Optimized views with -10 to 5° tilt and tool-free adjustment
- Supports 90° screen rotation for landscape or portrait display orientation
- Height-adjustable from 1200 to 1600 mm (47.2 to 63 in.)
- Height-adjustable shelf for laptop/AV accessories with 260 x 400 mm (10.2 x 15.7 in.) space and a rated load of 5 kg (11 lbs.)
- Premium-quality aluminum construction with powder coating
- Internal cable management for a clutter-free appearance
- Four lockable casters with highly durable polyurethane tread to support heavy weights and swift maneuverability
- Handle on pole for easy and convenient movement
- Meets VESA standards 200x200 to 600x400 e.g. 200x200, 300x200, 400x200, 300x300, 400x300, 400x400, 600x400
- Lifetime warranty

Specifications:

General

- Designed for most 37" - 86" screens
- Weight capacity: 50 kg (110 lbs.)
- Dimensions (D x W x H): 610 x 848 x 1420 - 1820 mm (24.02 x 33.39 x 55.9 - 71.65 in.)
- Net weight: 14.37 kg (31.68 lbs.)
- Gross weight: 16.45 kg (36.27 lbs.)
- Tilt: -10 to 5°
- Four caster wheels with four brakes and PU tread
- A/V shelf
 - Dimensions (D x W): 260 x 400 mm (10.2 x 15.7 in.)
 - Weight capacity: 5 kg (11 lbs.)
- Base dimensions (D x W): 610 x 848 mm (24 x 33.4 in.)
- VESA standards: 200x200 to 600x400 e.g. 200x200, 300x200, 400x200, 300x300, 400x300, 400x400, 600x400

Package Contents

- Aluminum Height-Adjustable Multimedia TV Trolley

- Installation hardware with instructions



