


ZOTAC
ZBOX


PICO PI430AJ WITH AIRJET (Barebone)

SKU: ZBOX-PI430AJ-GLB/BE

The ZBOX pico PI430AJ with AirJet is the world's first mini PC to incorporate Frore Systems' AirJet Solid State Active Cooling chip, which generates rapid airflow without fans. The more robust cooling hardware allows the PI430AJ to be equipped with more capable hardware such as an Intel Core i3 CPU, 8GB LPDDR5 fast memory, and a full-fledged M.2 NVMe SSD, all while impressively staying the size of a deck of playing cards.



HDMI
HIGH-DEFINITION MULTIMEDIA INTERFACE




Faster with
AirJet
by FRORE SYSTEMS



KEY FEATURES

- Ultra-compact 0.21 liter size
- DP via USB Type-C
- 8-core 8-thread Intel Core i3 processor
- AirJet Solid State Active Cooling
- Whisper Quiet Fanless Operation
- Native 4K output, up to 3 displays
- Wi-Fi 6 & Bluetooth 5.2, Gigabit LAN
- M.2 NVMe SSD Slot
- Micro SDHC/SDXC card reader
- 8GB LPDDR5 Memory



GIGABIT LAN



**Micro SDHC/SDXC
CARD READER**



WIFI 6



**ULTRA HD
4K**



**SOLID STATE
ACTIVE COOLING**

TECHNICAL SPECIFICATIONS

SPECIFICATIONS

- Intel Core i3-N300 processor (8-core, 0.8 GHz, up to 3.8 GHz)

DISPLAY OUTPUTS

- 1 x HDMI® Connector (Supports 4K 60Hz HDR as specified in the HDMI 2.0 Specification)
- 1 x DisplayPort 1.4 (up to 4096x2160@60Hz)
- DP1.4 via USB-C (3840x2160 @ 60Hz)
- Supports up to 3 displays

HARD DRIVE & MEMORY

- 1 x M.2 NVMe PCIe 3.0 x4 / SATA SSD slot (2230, 2242, 2280)
- 8GB LPDDR5 onboard memory

FRONT PORTS

- 2-in-1 card reader (Micro SDHC/SDXC)
- 2 x USB 3.2 Type-A ports
- 1 x USB 3.2 Type-C port
- Power button

REAR PORTS

- Power Connector
- Mic / Audio combo Jack
- 1 x 10/100/1000 Ethernet
- 1 x HDMI 2.0 port
- 1 x DisplayPort 1.4 port

CONNECTIVITY

- Wi-Fi 6
- Bluetooth 5.2

AUDIO OUTPUTS

- Onboard 8 Channel Digital Audio via HDMI
- Analog Stereo In / Out

SOFTWARE COMPATIBILITY

- Microsoft Windows 11 ready

INSIDE THE BOX

- ZOTAC ZBOX pico PI430AJ with AirJet
- AC adapter with universal plugs
- Mounting bracket
- Mount screws
- CTIA to OMTP audio adapter
- USB Flash Drive with drivers
- Quick Start Guide
- Warranty Card

MINI PC DIMENSIONS

- Length: 114.8mm (4.52in)
- Width: 76mm (2.99in)
- Height: 23.8mm (0.94in)

BOX DIMENSIONS

- Length: 178mm (7.01in)
- Width: 175mm (6.89in)
- Height: 53mm (2.09in)

©2023 ZOTAC Technology Ltd. All rights reserved. All company and/or product names may be trade names, trademarks and/or registered trademarks of the respective owners with which they are associated. Features, pricing, availability and specifications are subject to change without notice. ZOTAC Technology Limited does not warrant the accuracy, completeness or reliability of information, materials and other items contained on this website or server. No liability is assumed with respect to the use of the information contained herein. When accessing this website, users acknowledge that ZOTAC Technology Limited will not be liable in any event for any damages arising out of the use of this site or any websites linked to it.

For more information please visit:

ZOTAC.COM