




# MAGNUS EN374070W (Barebone)

SKU: ZBOX-EN374070W-BE/BE1/J/U/K/AUS

The all-new MAGNUS EN374070W upgraded with a 13th gen Intel Core i7 mobile processor and NVIDIA GeForce RTX 4070 Laptop GPU, is a formidable tailor-made machine for creative hobbyists and professionals alike. With a discrete yet powerful cooling solution, a comprehensive array of connectivity options, and as well as an extremely compact form-factor, the MAGNUS EN374070W fits a wide variety of creative workstation and studio needs, delivering impressive performance to help content creators and their masterpieces take form.



## KEY FEATURES

- Compact 2.65 liter size
- Thunderbolt 4
- 16-core 24-thread 13th Gen Intel Core i7 mobile processor
- GeForce RTX 4070 Laptop GPU
- Native 4K output, up to 3 displays
- Real-time Ray Tracing
- DLSS 3 Frame Generation
- NVIDIA® Studio Drivers Compatible
- Microsoft DirectX 12
- Killer Wi-Fi 6 & Bluetooth 5.2, Dual 2.5G LAN
- Gaming Ready / Creator Ready / 4K Ready



DUAL 2.5G LAN



THUNDERBOLT 4



WIFI 6



UHS-II SDXC CARD READER



ULTRA HD 4K



TRIPLE DISPLAY SUPPORT

## TECHNICAL SPECIFICATIONS

### SPECIFICATIONS

- Intel Core i7-13700HX processor (16-cores, 2.1 GHz, up to 5.0 GHz)
- GeForce RTX 4070 Laptop GPU 8GB GDDR6 128-bit, 2175MHz Boost Clock, up to 115W TDP

### DISPLAY OUTPUTS

- 1 x HDMI® Connector (Supports 4K 120Hz HDR, 8K 60Hz HDR, and Variable Refresh Rate as specified in the HDMI 2.1 Specification)
- 2 x DisplayPort 1.4a (up to 7680x4320@60Hz)
- Supports up to 3 displays

### HARD DRIVE & MEMORY

- 1 x M.2 NVMe PCIe 4.0 x4 SSD slot (2230/2242/2280/22110)
- 1 x M.2 NVMe PCIe 4.0 x4/SATA SSD slot (2230/2242/2280/22110)
- 2 x DDR5-4800 SO-DIMM Memory slots (Up to 64GB)

### FRONT PORTS

- UHS-II 3-in-1 card reader (SD/SDHC/SDXC)
- 1 x USB 3.1 port
- Power button and power LED
- Wi-Fi LED, Hard drive LED
- Thunderbolt 4 port (data only)

### REAR PORTS

- Power Connector
- 4 x USB 3.1 ports
- 2 x Killer 10/100/1000/2500 Ethernet
- Dual Wi-Fi antenna connector

### CONNECTIVITY

- WiFi 6
- Bluetooth 5.2

### AUDIO OUTPUTS

- Onboard 8 Channel Digital Audio via HDMI
- Analog Stereo In / Out

### SOFTWARE COMPATIBILITY

- Microsoft Windows 11 ready

### INSIDE THE BOX

- ZOTAC ZBOX MAGNUS EN374070W
- Power Cord (bundled cable type dependent on region)
- 2 x Wi-Fi Antenna
- USB Flash Drive with drivers
- Quick Start Guide

### MINI PC DIMENSIONS

- Length: 210mm (8.27in)
- Width: 203mm (7.99in)
- Height: 62.2mm (2.45in)

### BOX DIMENSIONS

- Length: 275mm (10.81in)
- Width: 265mm (10.4in)
- Height: 129mm (5.08in)

©2024 ZOTAC Technology Ltd. All rights reserved. All company and/or product names may be trade names, trademarks and/or registered trademarks of the respective owners with which they are associated. Features, pricing, availability and specifications are subject to change without notice. ZOTAC Technology Limited does not warrant the accuracy, completeness or reliability of information, materials and other items contained on this website or server. No liability is assumed with respect to the use of the information contained herein. When accessing this website, users acknowledge that ZOTAC Technology Limited will not be liable in any event for any damages arising out of the use of this site or any websites linked to it.

©2024 NVIDIA Corporation. NVIDIA, the NVIDIA logo, and GeForce are registered trademarks of NVIDIA Corporation in the U.S. and other countries. All rights reserved.

For more information please visit:

**ZOTAC.COM**