



4750RCHDW01FF3

Heavy Duty Rigid Case General Purpose Toolkit - 194 Pcs



PRODUCT DETAILS

- Heavy duty rigid case with wheels
- Aviation Mechanics, especially for mobile application and suitable for all airplanes
- Manufactured with structure of polypropylene copolymer resin
- Air pressure valve for maximum protection against extreme weather conditions
- Double robust bolt system for hermetic sealing
- TSA-approved padlock
- Includes 194 pieces
- Socketry, wrenches, screwdrivers, sizes: 1/4"; 3/8", pliers and hammers
- Foam codes: FF2B12, FF2B13, FF2B14, FF2B15 & FF2B16
- 4750RCHDW01 heavy-duty hardware rigid case with wheels
- 6700SM 1/4" socket hex 5.5, 6, 7, 8, 9, 10, 11, 12, 13 mm
- A6800DM 1/4" aerospace, long series socket 5.5, 6, 7, 8, 9, 10, 11, 12, 13 mm
- 6709M 1/4" socket driver hex 3, 4, 5, 6, 8 mm
- 6709PH 1/4" socket driver PH1, PH2, PH3
- 6709TORX 1/4" socket driver TORX® T8, T9, T10, T15, T20, T25, T27, T30, T40
- 6950SL 1/4" reversible ratchet and slim head, 6954 1/4" T-handle, 6956 1/4" spinner handle, 6958 1/4" breaker bar
- 6960/6962 1/4" extension bars 50, 100, 150 mm
- 6962L 1/4" extension bar 355 mm, 6966 1/4" universal joint, 6972H 1/4" bit holder, 7764 F 3/8" - M 1/4" adaptor
- 7400SM 3/8" socket short series 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 22 mm
- A7402DM 3/8" aerospace socket long series 10, 11, 12, 13, 14, 15, 16, 17, 18, 19 mm
- 7409M 3/8" socket driver hex 3, 4, 5, 6, 7, 8, 10 mm
- 7409TORX 3/8" socket driver TORX® T25, T27, T30, T40, T45, T50
- 7750SL 3/8" ratchet slim head
- 7760/7762 3/8" extension bars 75, 125, 250 mm
- 7766 3/8" universal joint, 7765 F 1/4" - M 3/8" adaptor, 8164-1/2 F 3/8" - M 1/2" adaptor, 7407H 3/8" socket holder 1/4" - 3/8"
- 111M combination wrench 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 21, 22 mm
- 6M open end wrench 6 x 7, 8 x 9, 10 x 11, 12 x 13, 14 x 15, 16 x 17, 18 x 19, 20 mm x 22 mm
- BE-9770 black hex L-key set, long ball end 9 pieces, 1.5, 2, 2.5, 3, 4, 5, 6, 8, 10 mm
- 9070C ERGO™ adjustable wrench chromed 6", 158 mm x 20 mm
- 1177-SCRIBE offset scriber 230 mm, 2535F2 magnetic pick up 1 kg, 7758 breaker bar, BFLA01 Q3 LED-torch, 7754 3/8" T-handle
- 808050P pistol handle ratcheting screwdriver, 808050S stubby ratcheting screwdriver
- 59S/31-1 bit set, 31 pieces, Phillips, Pozidriv, TORX®, hexagon, slotted
- 2047-0.8-4 offset screwdriver 0.8 mm x 4 mm x 100 mm
- 2047PR-1-2 double offset key for Phillips screws PH1-PH2
- BE-8020L ERGO™ screwdriver slotted 0.5 mm x 3 mm x 75 mm
- BE-8030 ERGO™ screwdriver slotted 0.6 mm x 3.5 mm x 75 mm
- BE-8155 ERGO™ screwdriver slotted 1.2 mm x 6.5 mm x 125 mm
- BE-8260 ERGO™ hex profile bolster screwdriver slotted 1.6 mm x 8 mm x 175 mm
- BE-8350 ERGO™ stubby slotted screwdriver 1 mm x 5.5 mm x 25 mm
- BE-8601/BE-8602 ERGO™ stubby screwdriver Phillips PH1 x 25 mm, PH2 x 25 mm
- BE-8610/BE-8630 ERGO™ screwdriver Phillips PH1 x 75 mm, PH2 x 100 mm, PH3 x 150 mm
- 2058-BR 1/4" bit-ratchet, 1544 feeler gauge, 2509 flexible pick-up tool 525 mm
- MTB-3-16-E measuring tape English 3 m, 2101GC-160IP ERGO™ side cutting pliers 160 mm
- 2427 GC-200IP ERGO™ snipe nose pliers, 200 mm
- 2430 GC-200 IP ERGO™ snipe nose chromed pliers 200 mm
- 2628 GC-160IP ERGO™ combination pliers, chrome finish, 160 mm
- 8224CIP ERGO™ slip joint pliers, 1150-1/2H/P calliper 150 mm
- 5515T-52 telescopic swivel head mirror Ø50 mm, 2820EF2 electricians' knife
- 481-300 DIN hammer 300 mm, 3625W-35 nylon tip hammer
- 3734 drift punch 3, 5, 8 mm
- 3735-4-120 centre punch 120 mm

Follow the Fish!



PRODUCT ATTRIBUTES

Product					
4750RCHDW01FF3	194	560 mm	365 mm	267 mm	20.47 kg

SET CONTENT



**Foam Inlay Socket Set for
4750RCHDW01 Heavy Duty Rigid
Case - 92 Pcs**
FF2B12



**Foam Inlay Wrench Set for
4750RCHDW01 Heavy Duty Rigid
Case - 39 Pcs**
FF2B13



**Foam Inlay Screwdriver Set for
4750RCHDW01 Heavy Duty Rigid
Case - 48 Pcs**
FF2B14



**Foam Inlay General Purpose Pliers
Set for 4750RCHDW01 Heavy Duty
Rigid Case - 9 Pcs**
FF2B15



**Foam Inlay Striking Set for
4750RCHDW01 Heavy Duty Rigid
Case - 6 Pcs**
FF2B16



**31 L Wheeled Heavy Duty Rigid
Case**
4750RCHDW01

