




Part Number : [351500214](#)

Product Description : VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 2 Circuits, Blue

Series Number : 35150

Status : Active

Product Category : Connector Housings



Documents & Resources

Drawings

[Drawing 351500214_sd.pdf](#)

3D Models and Design Files

[3D Model 351500214_stp.zip](#)

Specifications

[Application Specification 351500000AS_ENG-000.pdf](#)

[Packaging Specification PK-35150-002-001.pdf](#)

[Product Specification PS-35150-003-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	35150
Description	VersaBlade Hybrid Receptacle Housing, with Mounting Ears, 2 Circuits, Blue
Application	Power, Wire-to-Wire
Product Family	VersaBlade Wire-to-Wire Connector System
Product Name	VersaBlade
UPC	800753526815

Agency

CSA	LR19980
UL	E29179

Physical

Breakaway	No
Circuits (maximum)	2
Color - Resin	Blue
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	2.430/g
Number of Rows	1

Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	6.20mm
Pitch - Termination Interface	6.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +120°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
VersaBlade Hybrid Plug Housings	<u>35151</u>

Use with Part(s)

Description	Part Number
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Natural	<u>/content/molex/molex-dot-com/us/en/products/product-page.html/351500290.html</u>
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Red	<u>/content/molex/molex-dot-com/us/en/products/product-page.html/351500292.html</u>
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Yellow	<u>/content/molex/molex-dot-com/us/en/products/product-page.html/351500293.html</u>
VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Blue	<u>/content/molex/molex-dot-com/us/en/products/product-page.html/351500294.html</u>
VersaBlade Male Crimp Terminals	<u>35745</u>