



Part Number : [50579211](#)
Product Description : SL Crimp Housing,
Single Row, Version C, Front Ribs, 11 Circuits,
Black
Series Number : 70066
Status : Active
Product Category : Connector Housings
Engineering Number : 70066-0080



Documents & Resources

Drawings

[Drawing 050579211_sd.pdf](#)
[Packaging Design Drawing PK-70066-100-001.pdf](#)

3D Models and Design Files

[3D Model 050579211_stp.zip](#)

Specifications

[Product Specification PS-70400-001.pdf](#)
[Product Specification PS-70058-001.pdf](#)
[Product Specification PS-71851-001.pdf](#)
[Test Summary TS-70058-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)
- Eu RoHS

- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D

- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	70066
Description	SL Crimp Housing, Single Row, Version C, Front Ribs, 11 Circuits, Black
Application	Signal, Wire-to-Board
Comments	Version C
Product Family	SL Modular Connectors
Product Name	SL
UPC	800753784734

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	11
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	No

Material - Resin	Polyester Alloy
Net Weight	0.079/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
SL Vertical Single Row Headers	<u>70541</u>
SL Vertical Single Row Headers	<u>70543</u>
SL Vertical Single Row Headers	<u>70545</u>
SL Right-Angle Single Row Headers	<u>70551</u>
SL Right-Angle, Single Row, Low Profile Headers	<u>70553</u>
SL Right-Angle Single Row Headers	<u>70555</u>
SL Right-Angle, Single Row, Low Profile, Surface Mount Headers	<u>70634</u>
SL Vertical, Single Row, Surface Mount Headers	<u>74099</u>

Use with Part(s)

Description	Part Number
SL Female Terminals	<u>70058</u>
SL Female Terminals	<u>71851</u>