



Part Number : [190020012](#)

Product Description : Avikrimp Fully Insulated Quick Disconnect, Female, for 18-22 AWG Wire, Metal Strip

Series Number : 19002

Status : Active

Product Category : Quick Disconnects

Engineering Number : AA-5271Z



Documents & Resources

Drawings

[Drawing 190020012_sd.pdf](#)

3D Models and Design Files

[3D Model 190020012_stp.zip](#)

Specifications

[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-014-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19002
Description	Avikrimp Fully Insulated Quick Disconnect, Female, for 18-22 AWG Wire, Metal Strip
Product Family	Standard Quick-Disconnect Terminals
Product Name	Avikrimp
Type	Quick Disconnect
UPC	800753027077

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	300V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Red
Flammability	94V-2
Gender	Female
Glow-Wire Capable	No
Insulated	Fully
Insulation	Nylon (PA)

Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.044/g
Orientation	Straight
Packaging Type	Reel
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	4.75mm
Temperature Range - Operating	-65° to +105°C
Wire Insulation Diameter	3.17mm max.
Wire Size (AWG)	18, 20, 22

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Mini-Mac Applicator	<u>0638812000</u>