




Part Number : [190670085](#)
Product Description : NylaKrimp Funnel Entry
Ring Tongue Terminal for 4 AWG Wire, Stud
Size 1/2" (M12)
Series Number : 19067
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : F-969-12



Documents & Resources

Drawings
[Drawing 190670085_sd.pdf](#)

3D Models and Design Files
[3D Model 190670085_stp.zip](#)

Specifications
[Product Specification PS-19902-013-001.pdf](#)
[Product Specification PS-19902-016-001.pdf](#)
[Product Specification PS-19902-011-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19067
Description	NylaKrimp Funnel Entry Ring Tongue Terminal for 4 AWG Wire, Stud Size 1/2" (M12)
Keyword	Ring Terminal, Ring Terminals
Product Family	Solderless Terminals
Product Name	NylaKrimp
Type	Ring
UPC	800753066564

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Flammability	94V-2
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Net Weight	14.713/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	1/2" (M12)

Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	12.95mm max.
Wire Size (AWG)	4

Application Tooling

Global

Description	Part Number
Manual Putt Pump Hydraulic System, Die set required	<u>0192860117</u>
Die Set (Large) for the HHLS Hydraulic Crimper	<u>0192890007</u>
Hydraulic Dieless Crimping Tool	<u>0638161700</u>
PremiumGrade Hand Crimp Tool for 2-8 AWG Terminals	<u>0640013900</u>
Hand Crimp Tool for 4 AWG Insulated Ring Terminals	<u>0640017870</u>