



Part Number : [190980024](#)


Product Description : Krimptite Snap Spade Terminal, for 18-22 AWG Wire, Stud Size 10 (M5), 17.60mm Length

Series Number : 19098

Status : Active

Product Category : Ring and Spade Terminals

Engineering Number : AA-1715-10



---

## Documents & Resources

### Drawings

[Drawing 190980024\\_sd.pdf](#)

### 3D Models and Design Files

[3D Model 190980024\\_stp.zip](#)

### Specifications

[Product Specification PS-19902-013-001.pdf](#)

[Product Specification PS-19902-011-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

### [Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

### [Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Ring and Spade Terminals
Series	19098
Description	Krimptite Snap Spade Terminal, for 18-22 AWG Wire, Stud Size 10 (M5), 17.60mm Length
Keyword	Spade Terminal, Spade Terminals
Product Family	Solderless Terminals
Product Name	Krimptite
Type	Spade Snap
UPC	800755081411

### Agency

CSA	LR18689
UL	E32244

### Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.555/g
Packaging Type	Bag
Stud Size	10 (M5)
Wire Size (AWG)	18, 20, 22
Wire Size mm <sup>2</sup>	0.35-0.80

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Application Tooling

### Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm <sup>2</sup> - 0.5mm <sup>2</sup>	<u>0640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>0640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>0640160038</u>

---

This document was generated on Sep 26, 2023