




Part Number : [455870004](#)
Product Description : Mini-Fit Jr. Receptacle Housing, Third Generation Polarization Type for PCIe Applications, Dual Row, UL 94V-0, 8 Circuits, Black
Series Number : 45587
Status : Active
Product Category : Connector Housings



Documents & Resources

Drawings
[Drawing 455870004_sd.pdf](#)
[Packaging Design Drawing PK-5557-002-000.pdf](#)

3D Models and Design Files
[3D Model 455870004_stp.zip](#)

Specifications
[Product Specification PS-5556-001-001.pdf](#)
[Product Specification PS-45558-001-001.pdf](#)
[Test Summary TS-5556-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)
- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Housings
Series	45587
Description	Mini-Fit Jr. Receptacle Housing, Third Generation Polarization Type for PCIe Applications, Dual Row, UL 94V-0, 8 Circuits, Black
Application	Power, Wire-to-Board
Product Family	Mini-Fit Family Power Connectors
Product Name	Mini-Fit Jr.
UPC	191128444385

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	8
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.812/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No

Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini-Fit Jr. Right-Angle Dual Row Headers	<u>45586</u>

Use with Part(s)

Description	Part Number
Mini-Fit Female Crimp Terminals	<u>5556</u>