

Part Number: 508029101

Product Description: 2.50mm Pitch Mini-Latch Crimp Terminal, Female, Brass, Bag

Series Number: 50802

Status: Active

**Product Category : Crimp Terminals** 

Packaging Alternative: 0508029001 (Reel)



#### **Documents & Resources**

#### **Drawings**

Drawing 508029101\_sd.pdf

3D Models and Design Files

3D Model 508029101\_stp.zip

### Specifications

Product Specification 511910000-PS-000.pdf Product Specification PS-51191-003-001.pdf

## **Product Environment Compliance**

### Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	<b>©</b>
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

## **Part Details**

#### General

Status	Active
Category	Crimp Terminals
Series	50802
Description	2.50mm Pitch Mini-Latch Crimp Terminal, Female, Brass, Bag
Application	Signal, Wire-to-Board, Wire-to-Wire
Product Family	Mini-Latch Wire-to-Board / Wire-to- Wire Connector System
Product Name	Mini-Latch
UPC	800753370616

### Electrical

Current - Maximum per Contact	3.0A

# Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	56.000/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.15-1.90mm
Wire Size (AWG)	22, 24, 26, 28

Wire Size mm²	N/A
	1

# Use with Part(s)

Description	Part Number
Mini-Latch Receptacle Housings	<u>51191</u>

# **Application Tooling**

### Global

Description	Part Number
Extraction and Activation Tool	0638132700
Hand Crimp Tool for 2.50mm Pitch SPOX Crimp Terminal, 22-28 AWG	0638281900

# **Application Tooling**

# Japan

Description	Part Number
Hand Crimp Tool JHTR5907	0011260095

This document was generated on Sep 26, 2023