



**Part Number :** [734200391](#)  
**Product Description :** 50 Ohms, SMP-MAX Plug, Straight, Gold Plated Body, Press-Fit Panel Mount, Slide Type, Catcher's Mitt, Tray  
**Series Number :** 73420  
**Status :** Active  
**Product Category :** RF / Coaxial Connectors



Documents & Resources

**Drawings**  
[Drawing 734200391\\_sd.pdf](#)

Product Environment Compliance

Compliance

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                          |
| China RoHS         |  |
| EU ELV             | Not Relevant                                                                          |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                                                        |
| REACH SVHC         | Contains Lead per D(2023)3788-DC (14 Jun 2023)                                        |
| EU RoHS            | Compliant with Exemption 6(c) per EU 2015/863                                         |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

## Part Details

### General

|                |                                                                                                            |
|----------------|------------------------------------------------------------------------------------------------------------|
| Status         | Active                                                                                                     |
| Category       | RF / Coaxial Connectors                                                                                    |
| Series         | 73420                                                                                                      |
| Description    | 50 Ohms, SMP-MAX Plug, Straight, Gold Plated Body, Press-Fit Panel Mount, Slide Type, Catcher's Mitt, Tray |
| Product Family | 5G RF Connector and Cable Solutions                                                                        |
| Product Name   | SMP-MAX                                                                                                    |
| Style          | Panel                                                                                                      |
| Type           | Subminiature                                                                                               |
| UPC            | 884982584266                                                                                               |

### Electrical

|                 |                             |
|-----------------|-----------------------------|
| Frequency       | 10 GHz                      |
| Impedance       | 50Ω                         |
| Power / Voltage | VOLTAGE: 330 Vrms@Sea Level |

### Physical

|                       |           |
|-----------------------|-----------|
| Gender                | Plug      |
| Keying to Mating Part | None      |
| Net Weight            | 2.226/g   |
| Orientation           | Straight  |
| Packaging Type        | Tray      |
| Panel Mount           | Yes       |
| Panel Mount Method    | Press-Fit |
| PCB Mounting          | N/A       |
| Wire/Cable Type       | N/A       |

### Solder Process Data

|                              |     |
|------------------------------|-----|
| Lead-Free Process Capability | N/A |
| Max-Cycle                    | 2   |
| Max-Temp                     | 260 |

---

---

This document was generated on Sep 26, 2023