



**Part Number :** [2053425128](#)

**Product Description :** 2.00mm Pitch, Pico-Lock Female Crimp Terminal, Gold (Au) Plating, 24-26 AWG

**Series Number :** 205342

**Status :** Active

**Product Category :** Crimp Terminals



---

## Documents & Resources

### Drawings

[Drawing 2053425128\\_sd.pdf](#)

### 3D Models and Design Files

[3D Model 2053425128\\_stp.zip](#)

### Specifications

[Application Specification 2053410000-AS-000.pdf](#)

[Packaging Specification 2053429200-SPK-200.pdf](#)

[Product Specification 2053410000-PS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

### [Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

### [Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Crimp Terminals
Series	205342
Description	2.00mm Pitch, Pico-Lock Female Crimp Terminal, Gold (Au) Plating, 24-26 AWG
Application	Power, Signal, Wire-to-Board, Wire-to-Wire
Product Family	Pico-Lock Connector System
Product Name	Pico-Lock
UPC	191130510030

### Electrical

Current - Maximum per Contact	6.5A
Voltage - Maximum	250V AC (RMS)/DC

### Physical

Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Net Weight	65.870/mg
Packaging Type	Reel
Plating min - Mating	0.100µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	0.85-1.30mm
Wire Size (AWG)	24, 26
Wire Size mm <sup>2</sup>	N/A

---

## Application Tooling

### Global

Description	Part Number
FA2 Mechanical Feed Crimp Applicator for Pico-Lock 2.0 Crimp Terminals, 24-26 AWG	<u>2130691500</u>
FA2 Pneumatic Feed Crimp Applicator for Pico-Lock 2.0 Crimp Terminals, 24-26 AWG	<u>2130691510</u>
Hand Crimp Tool for 2.00mm Pitch Pico-Lock Terminals, 24-26 AWG	<u>2133090900</u>
Extraction and Activation Tool	<u>0638132700</u>

## Application Tooling

### Japan

Description	Part Number
S-1 Applicator for 2.00mm Pitch Pico-Lock Female Crimp Terminals, 24-26 AWG	<u>2111423710</u>