



Part Number : [2162851062](#)
Product Description : MX150 Female-to-MX150 Female Off-the-Shelf (OTS) Cable Assembly, Dual Row, 300.00mm Length, Tin (Sn) Plating, 6 Circuits, Black
Series Number : 216285
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents & Resources

Drawings
[Drawing 2162851062_sd.pdf](#)
[Packaging Design Drawing 2162801021-001.pdf](#)

3D Models and Design Files
[3D Model 2162851062_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	216285
Description	MX150 Female-to-MX150 Female Off-the-Shelf (OTS) Cable Assembly, Dual Row, 300.00mm Length, Tin (Sn) Plating, 6 Circuits, Black
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	MX150-to-MX150
Product Family	MX150 Sealed and Unsealed Connector System
Product Name	MX150
Type	Discrete Wire Assembly, Sealed Assembly
UPC	193264714575

Electrical

Current - Maximum per Contact	22.0A
Voltage - Maximum	14V DC

Physical

Cable Length	300.00mm
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin

Material - Resin	SPS/Nylon
Net Weight	629.400/g
Number of Rows	2
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	3.50mm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	TXL Stranded
Wire Insulation Diameter	2.70mm max.
Wire Size (AWG)	14

Mates With / Use With

Mates with Part(s)

Description	Part Number
MX150 Mat-Sealed Dual Row Male Connector Assemblies	<u>33482</u>