



Part Number : [192210380](#)


Product Description : Compression Style Ring  
Tongue Terminal for 2 AWG Wire, Stud Size  
3/8" (M9), Unplated

Series Number : 19221

Status : Active

Product Category : Ring and Spade Terminals

Engineering Number : BCL-238



---

## Documents & Resources

### Drawings

[Drawing 192210380\\_sd.pdf](#)

### 3D Models and Design Files

[3D Model 192210380\\_stp.zip](#)

### Specifications

[Product Specification PS-19902-017-001.pdf](#)


[Product Specification PS-19901-017-001.pdf](#)

[Product Specification PS-19902-011-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

### [Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

## Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Ring and Spade Terminals
Series	19221
Description	Compression Style Ring Tongue Terminal for 2 AWG Wire, Stud Size 3/8" (M9), Unplated
Comments	Heavy Duty
Keyword	Ring Terminal, Ring Terminals
Product Family	Battery Cable Lugs
Product Name	Battery Cable Lug
Type	Ring
UPC	800753064386

#### Agency

CSA	LR18689
UL	E32244

#### Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Unplated
Net Weight	11.358/g
Packaging Type	Bag
Stud Size	3/8" (M9)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	N/A

Wire Size (AWG)	2
-----------------	---

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

### Application Tooling

#### Global

Description	Part Number
Hand Crimp Tool for Eyelet Style Copper Lug Terminals 8-4/0 AWG	<u>0192840034</u>
Manual Putt Pump Hydraulic System, Die set required	<u>0192860117</u>
Die Set (Large) for the HHLS Hydraulic Crimper	<u>0192900010</u>
Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	<u>0192940008</u>
Square "DIN" style dies for 2 AWG	<u>0640037970</u>