


PRODUCT

ESD Grid Tape

Our conductive grid tape is made from silicone free, low residue polypropylene with a self adhesive dissipative co-polymer backing and a conductive grid surface layer.

For use in static free workstations where ESD sensitive components are handled.

Both conductive surface and dissipative adhesive layer are low-tribocharging at 50% RH.



FEATURES

- Polypropylene self adhesive tape with conductive grid pattern on the surface
- Supplied on a cardboard core (Core Size: 3")
- Silicone free, with low residue
- Grid pattern includes the ESD logo to EN 61340-5
- Typically used for sealing primary packaging

To request a quotation or for more information, please call **+44 (0)1473 836200**
email info@antistat.co.uk or visit www.antistat.co.uk

IMPORTANT: This data sheet and its contents (the "Information") belong to Antistat or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Antistat assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Antistat was aware of the possibility of such loss or damage arising) is excluded. © 2021 Antistat.

No.	Parameter	Measurement	Testing Standard	Testing Result
1	Solid Content	%	53.5-55%	54%
2	Peeling Strength by Angle of 180 Degrees	N/25mm	≥5	6.5
3	Holding Force at 0°C	mm/h	≤3	0
4	Initial Adhesion (Steel Ball)	G	≥13	13
5	Width Tolerance	mm	±0.5	OK
6	Length Tolerance	m	≥0	OK
7	Total Thickness	um	60	61
8	Roll Core Inner Diameter	mm	76	76
9	Tensile Strength	n/25mm	≥30	42
10	Elongation Rate	%	100 - 180	159
11	OPP Film Thickness	u	38	38
12	Pressure Sensitive Adhesive Thickness	u	22	23
13	Surface Resistance	Ohms	10 ⁶ - 10 ⁹	10 ⁷

NOTES

- Replace regular adhesive tapes with antistatic tapes complying with EN 61340-5
- “All generators of electrostatic charges, such as untreated plastic films, foams, synthetic fibres, adhesive tapes, etc., must be prohibited and should be kept away from the EPA [ESD protected area].” (EN 61340-5-2 section 6)
- “EPA should never have any electrostatic generative adhesive tapes or labels, as these can cause very high potentials when applied or stripped off.” (EN 61340-5-1 section 7.4)

RoHS DIRECTIVE

In accordance with the RoHS Directive 2002/95EC, and its amendment directives, conductive grid tape was tested using method: 3540C/3550B for PBB/PBDE content.

Test results by chemical method (Unit: mg/kg)

Cadmium (Cd) - not detected	Lead (Pb) - not detected
Mercury (Mg) - not detected	Hexavalent Chromium (CrVi) - not detected
Polybrominated Biphenyl - not detected	Polybrominated Diphenylethers - not detected

Product Code	Description	Size	Additional notes
154-0140	ESD Grid Tape	12mm x 40m	Per Roll
054-0109	ESD Grid Tape	24mm x 40m	Per Roll
054-0111	ESD Grid Tape	19mm x 40m	Per Roll
054-0114	ESD Grid Tape	48mm x 40m	Per Roll

To request a quotation or for more information, please call **+44 (0)1473 836200**
 email info@antistat.co.uk or visit www.antistat.co.uk

IMPORTANT: This data sheet and its contents (the "Information") belong to Antistat or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Antistat assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Antistat was aware of the possibility of such loss or damage arising) is excluded. © 2021 Antistat.