



| 31  | 02 09 500 1034 | 66 x 2,54 = 167,64 | 172,62         |
|-----|----------------|--------------------|----------------|
| 30  | 02 09 500 1033 | 64 x 2,54 = 162,56 | 167,54         |
| 29  | 02 09 500 1032 | 62 x 2,54 = 157,48 | 162,46         |
| 28  | 02 09 500 1031 | 60 x 2,54 = 152,40 | 157,38         |
| 27  | 02 09 500 1030 | 58 x 2,54 = 147,32 | 152,30         |
| 26  | 02 09 500 1029 | 56 x 2,54 = 142,24 | 147,22         |
| 25  | 02 09 500 1028 | 54 x 2,54 = 137,16 | 142,14         |
| 24  | 02 09 500 1027 | 52 x 2,54 = 132,08 | 137,06         |
| 23  | 02 09 500 1026 | 50 x 2,54 = 127,00 | 131,98         |
| 22  | 02 09 500 1025 | 48 x 2,54 = 121,92 | 126,90         |
| 21  | 02 09 500 1024 | 46 x 2,54 = 116,84 | 121,82         |
| 20  | 02 09 500 1023 | 44 x 2,54 = 111,76 | 116,74         |
| 19  | 02 09 500 1022 | 42 x 2,54 = 106,68 | 111,66         |
| 18  | 02 09 500 1021 | 40 x 2,54 = 101,60 | 106,58         |
| 17  | 02 09 500 1020 | 38 x 2,54 = 96,52  | 101,50         |
| 16  | 02 09 500 1019 | 36 x 2,54 = 91,44  | 96,42          |
| 15  | 02 09 500 1018 | 34 x 2,54 = 86,36  | 91,34          |
| 14  | 02 09 500 1017 | 32 x 2,54 = 81,28  | 86,26          |
| 13  | 02 09 500 1016 | 30 x 2,54 = 76,20  | 81,18          |
| 12  | 02 09 500 1015 | 28 x 2,54 = 71,12  | 76,10          |
| 11  | 02 09 500 1014 | 26 x 2,54 = 66,04  | 71,02          |
| 10  | 02 09 500 1013 | 24 x 2,54 = 60,96  | 65,94          |
| 9   | 02 09 500 1012 | 22 x 2,54 = 55,88  | 60,86          |
| 8   | 02 09 500 1011 | 20 x 2,54 = 50,80  | 55,78          |
| 7   | 02 09 500 1010 | 18 x 2,54 = 45,72  | 50,70          |
| 6   | 02 09 500 1009 | 16 x 2,54 = 40,64  | 45,62          |
| 5   | 02 09 500 1008 | 14 x 2,54 = 35,56  | 40,54          |
| 4   | 02 09 500 1007 | 12 x 2,54 = 30,48  | 35,46          |
| 3   | 02 09 500 1006 | 10 x 2,54 = 25,40  | 30,38          |
| 2   | 02 09 500 1005 | 8 x 2,54 = 20,32   | 25,30          |
| 1   | 02 09 500 1004 | 6 x 2,54 = 15,24   | 20,22          |
| no. | version        | n x 2,54 = A       | length L ± 0,1 |

|                                               |                     |                                  |                       |                           |                                                          |                        |
|-----------------------------------------------|---------------------|----------------------------------|-----------------------|---------------------------|----------------------------------------------------------|------------------------|
|                                               | All rights reserved | Created by<br>HASELOH            | Inspected by<br>WOLF  | Standardisation<br>KÖHLER | Date<br>2020-09-22                                       | State<br>Final Release |
|                                               | Department EL PD    | Title<br>har-modular fixing rail |                       |                           | Doc-Key / ECM-Nr.<br>100813490/UGD/002/D<br>500000178722 |                        |
| HARTING Electronics GmbH<br>D-32339 Espelkamp |                     | Type<br>TB                       | Number<br>020950010XX |                           | Rev.<br>D                                                | Page<br>1/1            |