



MAGNUS ONE ERP54060C (Barebone)

SKU: ZBOX-ERP54060C-BE/BE1/J/U/K/AUS

The all-new MAGNUS ONE retains the 8.3 liter chassis of its predecessor, but the internals have been thoroughly upgraded with cutting-edge hardware, including a 13th gen Intel® Core™ i5 processor for faster processing, a ZOTAC GAMING GeForce RTX™ 4060 graphics card for high-fidelity ray-traced graphics and AI-accelerated features such as DLSS3.5, and other upgrades such as a UHS-II card reader for faster file transfers from SD cards. Pair those with upgradable memory and storage and a full-range of connectivity options including Killer networking, and you have a capable machine that could deliver the best experience for daily tasks, gaming, entertainment, content creation and business.



KEY FEATURES

- Compact 8.3 liters
- 500W 80+ Platinum PSU
- Thunderbolt 4
- 10-core 16-thread 13th Gen Intel Core i5 processor
- GeForce RTX 4060 GPU
- Native 4K output, up to 4 displays
- Real-time Ray Tracing
- DLSS 3 Frame Generation
- NVIDIA® Studio Drivers Compatible
- NVIDIA® G-SYNC® compatible
- Microsoft DirectX 12
- Killer Wi-Fi 6 & Bluetooth 5.2, Dual LAN
- Gaming Ready / Creator Ready / 4K Ready / VR Ready




DUAL LAN



THUNDERBOLT 4



WIFI 6



UHS-II SDXC CARD READER



ULTRA HD 4K



QUAD DISPLAY SUPPORT

TECHNICAL SPECIFICATIONS

SPECIFICATIONS

- Intel Core i5-13400 processor (10-core 1.8 GHz, up to 4.6 GHz)
- ZOTAC GAMING GeForce RTX 4060 8GB GDDR6 (Graphics card compatibility - Power: up to 220W, Width: dual-slot, Length: 230mm / 9.06in)
- 500W 80+ Platinum PSU

DISPLAY OUTPUTS

- 1 x HDMI 1.4 (up to 3840x2160@30Hz) (integrated)
- HDMI® Connector (Supports 4K 120Hz HDR, 8K 60Hz HDR, and Variable Refresh Rate as specified in the HDMI 2.1a Specification)
- 3 x DisplayPort 1.4a (up to 7680x4320@60Hz)
- Up to Quad Display Support

HARD DRIVE & MEMORY

- 2 x DDR5-4800 SO-DIMM slots (up to 64GB)
- 1 x 2.5-inch SATA 6.0 Gb/s HDD/SSD bay
- 1 x M.2 NVMe PCIe 4.0 x4 NVMe / SATA SSD slot (2242, 2280)
- 1 x M.2 NVMe PCIe 4.0 x4 SSD slot (2242/2280/22110)

FRONT PORTS

- UHS-II 3-in-1 card reader (SD/SDHC/SDXC)
- 2 x USB 3.0 ports (1 Type-C)
- Power button and power LED
- Wi-Fi LED, Hard drive LED

REAR PORTS

- Power Connector
- 2 x USB 3.0 ports
- 4 x USB 3.1 ports
- 1 x 10/100/1000 Ethernet
- 1 x Killer 10/100/1000/2500 Ethernet
- Dual Wi-Fi antenna connector
- 1 x Thunderbolt 4 port

CONNECTIVITY

- WiFi 6
- Bluetooth 5.2

AUDIO OUTPUTS

- Onboard 8 Channel Digital Audio via HDMI
- Analog Stereo In / Out

SOFTWARE COMPATIBILITY

- Microsoft Windows 11 ready

INSIDE THE BOX

- ZOTAC ZBOX MAGNUS ONE ERP54060C
- Power Cord (bundled cable type dependent on region)
- 2 x Wi-Fi Antenna
- USB Flash Drive with drivers
- Quick Start Guide

MINI PC DIMENSIONS

- Length: 265.5mm (10.45in)
- Width: 126mm (4.96in)
- Height: 249mm (9.8in)

BOX DIMENSIONS

- Length: 440mm (17.32in)
- Width: 327mm (12.87in)
- Height: 205mm (8.07in)



©2023 ZOTAC Technology Ltd. All rights reserved. All company and/or product names may be trade names, trademarks and/or registered trademarks of the respective owners with which they are associated. Features, pricing, availability and specifications are subject to change without notice. ZOTAC Technology Limited does not warrant the accuracy, completeness or reliability of information, materials and other items contained on this website or server. No liability is assumed with respect to the use of the information contained herein. When accessing this website, users acknowledge that ZOTAC Technology Limited will not be liable in any event for any damages arising out of the use of this site or any websites linked to it.

©2023 NVIDIA Corporation. NVIDIA, the NVIDIA logo, and GeForce are registered trademarks of NVIDIA Corporation in the U.S. and other countries. All rights reserved.

For more information please visit:

ZOTAC.COM