


36039-00019: GIANT 28 PRO 230-240~50-GR-TS EU 2L C/AVV.PRO-LAVOR-

Validity date: 05/11/2024




Pos.	Old code	Code	Description
0	5.011.0233	10002-05701	CAREN. POSTERIORE GIANT-NERO-C/RUOTE SILVER
0	5.011.0516	10002-05973	ASSIEME AVVOLG.COMPLETO+MANICO GIANT C/ADATT.PIST.S'09
0	5.001.0812	34005-00417	MTP.PT03 125H110ALL 230-240/50 D.12-12' TS IN.1,7 TEST.OTT.
1	4.008.2238	00042-01514	COPERTURA ANT. GIANT/ALASKA-GR.CH.-RAL.7046 C/TAMP.-LAVOR-
2	4.008.1492	00026-00777	MANOPOLA INTERRUTTORE VERTIGO-SILVER-VERNIC.
3	4.008.1726	00039-01022	COP.SCATOLA ELETTR.GIANT/ALASKA-NERO-
4	3.401.0225	00057-01205	INTERRUTTORE ROTAT.BIPOLARE 16A(0-1)C/PERNO L=15
5	4.008.0776	00039-00976	COPERCHIO USCITA CAVI MOTORE ELETTR. NERO
6	3.404.0095	00058-01455	CONDENSATORE 55MF 450V D.50X94 F/M
7	4.008.0922	00032-00142	COPRIVENTOLA X MOTORE '96 S/GRIGLIA S/FINESTRE
8	4.018.0135	00080-02177	TUBO 1/4 L=800 21MPA R1 X AVV.GIANT
9	6.005.0637	10001-09140	KIT AVV.PRO GIANT(S/TUBO)-LAVOR-
10	4.008.1723	00026-01736	MANICO ALTO GIANT/ALASKA-GR.CHIARO-RAL.7046
11	4.008.1724	00042-01251	PORTACCESSORI GIANT/ALASKA-NERO-
13	4.008.1727	00035-00618	DISTANZIALE APPOGGIO POMPA GIANT-NERO-
14	4.013.0735	00042-02164	CAREN. ANT. GIANT-NERO-
16	4.008.1728	00054-00779	SERBATOIO GIANT/ALASKA(X MOTORE D.125)
17	4.008.1554	00008-01058	TAPPO BLU PANT.PQ-293C PER SERBATOIO
18	4.012.0150	00058-02024	CAVO H05VV-F 3X1,5 MT.5,4 SP.SCHUKO ANTISP.F/F
19	7.100.2415	22001-04230	MANUALE SPEC.GIANT/FUSION C/AVV.PRO+AD.+CE LAVOR 27L A5 16F
21	6.001.0089	00080-02524	PISTOLA S'10Y C/ATT.RAP. INTEGR.-M22

Pos.	Old code	Code	Description
22	3.712.0029	00080-01758	LANCIA ANG. VARIOJET 033 VERDE(3301106300A)TECOMEC 472387125
23	6.002.0392C	00080-02808	LANCIA ROTOX L=430 INCLINATA S/COPERTURA M22 D.1,20(04)
24	3.100.0405	00009-02316	TRANSPARENT QUICK COUPLING INLET CONNECTOR WITH INSPECTIONAB
25	6.003.0045C	00009-02964	ADATTATORE M22X1,5+ATTACCO INN.RAPIDO C/FILETTO METAL.

10002-05701: CAREN. POSTERIORE GIANT-NERO-C/RUOTE SILVER

Validity date: 05/11/2024






Pos.	Old code	Code	Description
1	4.007.0337	00071-02681	ASSALE RUOTE BEST D.20 L=330MM
2	4.013.0734	00042-02163	CAREN. POSTERIORE GIANT/ALASKA-NERO-
3	6.005.0238	10001-08847	KIT 221 LW RUOTE+FERMO BEST/H URRICANE/RENO

10002-05973: ASSIEME AVVOLG.COMPLETO+MANICO GIANT C/ADATT.PIST.S'09


Validity date: 05/11/2024

D50110516/01



Pos.	Old code	Code	Description
0	5.009.1156	10002-05519	AVV.COMPLETO PRO '14+TUBO 8M M22(GIANT 24 PRO)
1	4.008.1723	00026-01736	MANICO ALTO GIANT/ALASKA-GR.CHIARO-RAL.7046
3	5.011.0210	10002-05680	ASSIEME MANOV.C/PERNO L=102,5+IMP.LUNGA '14-N-


Validity date: 05/11/2024



Pos.	Old code	Code	Description
0	5.008.0234	10002-02128	TESTATA PT'03 D.12 OTT.C/TAPPI FIL.(TEN.NERE TELATE)
0	5.009.1016	00059-00913	ASS.MOTORE D.125H110ALL 230-240/50 2P+PIATT.12'
0	5.007.0251	10002-10085	C.GUIDA PT03 PIST.D.12 INOX TORN.TS 17KG C/ASP.(FIL)
1	6.005.0251	10001-08859	KIT 234 LW VENTOLA+ANELLO
3	4.007.0416	00045-00441	CUSCINETTO REGGISPINTA A SFERE 35X58X12 PER PT03(180BAR)
5	6.005.0134	10001-08753	KIT 125 LW ANELLI APP.TENUTA OTTONE+DISTANZIALI PT D.12

10002-05519: AVV.COMPLETO PRO '14+TUBO 8M M22(GIANT 24 PRO)

Validity date: 05/11/2024




Pos.	Old code	Code	Description
1	6.005.0643	10001-09146	KIT RACC.AD OCCHIELLO+FORCELLA PER AVV.VERS.'14
2	4.006.0395	00053-00508	PERNO 3/8G PER RACCORDO AD OCCHIELLO AVV.VERS.'14
3	4.008.1624	00040-01058	SEMIAVV.LATO INGRESSO VERS.'14
4	4.008.1625	00040-01059	SEMIAVV.LATO MANOVELLA VERS.'14
5	4.018.0135	00080-02177	TUBO 1/4 L=800 21MPA R1 X AVV.GIANT
6	4.618.0212	00080-02412	TUBO R1 1/4 MAX 23MPA MT.8 RACC.3/8-GIR.1/4F C/1MANICHETTA

10002-02128: TESTATA PT'03 D.12 OTT.C/TAPPI FIL.(TEN.NERE TELATE)

Validity date: 05/11/2024

D50080234/01




Pos.	Old code	Code	Description
1	6.005.0315	10001-08918	KIT 287 LW VALV.ASP./MAND.+TAPPI OTT.FIL.PT' 03
2	4.006.0340	00027-00712	TESTATA PT03 OTT.LAVOR C/FIL.X TAPPI VALV.S/MANOM.
3	6.005.0316	10001-08919	KIT 288 ANELLI TENUTA ACQUA MARRONI PT TEST.OTT.D.12

00059-00913: ASS.MOTORE D.125H110ALL 230-240/50 2P+PIATT.12'

Validity date: 05/11/2024


D50091016/01



Pos.	Old code	Code	Description
0	5.Y09.0587	00022-01974	FLANGIA ANT. X PT03 D.125H110 C/FILETTI
1	5.002.0149	10002-04933	CARCASSA'96 D125H110ALL 230-240/50 2P C/TERM.
2	5.005.0072	00033-00252	ALBERO ROTORE D.65 H.110 X MOT.125ALL PT03 230/50
4	3.001.0002	00045-00348	CUSCINETTO OBLIQUO A SFERA 20X52X15 7304 B
5	4.005.0225	00067-00189	PIATTELLO 12GR PER PT03 CUSCIN.REGGISPINTA SFERE

10002-10085: C.GUIDA PT03 PIST.D.12 INOX TORN.TS 17KG C/ASP.(FIL)

Validity date: 05/11/2024




Pos.	Old code	Code	Description
1	5.009.0596	10002-05273	ASS.V.COMP.C/TS PT03 CAVO L=530 MOLLA 17KG(COPRIF.VERDE)
2	6.005.0277	10001-08881	KIT INIETTORE 1,7 PORTAG.FIL.+VALV.RITEGNO PT'03
3	6.005.0079	10001-08715	KIT 79 LW ANELLI TENUTA OLIO X PARTNER D.12/FIBRA
4	6.005.0226	10001-08836	KIT 'O-RING PER PT03'
5	4.005.0263	00040-00960	CORPO GUIDA PISTONI PT03 C/FORO ASP.DET.FILET.
6	6.005.0426	10001-09024	KIT 371 PISTONI ACCIAIO FERMO TORN.+MOLLE(VERTIGO)

00022-01974: FLANGIA ANT. X PT03 D.125H110 C/FILETTI

Validity date: 05/11/2024

D5Y090587/01



Pos.	Old code	Code	Description
1	4.Y05.0226	00022-01682	FLANGIA ANT.MOTORE D.125H110 PT03 LAV.C/FILETTI
2	3.201.0001	00003-00216	ANELLO TENUTA 20/35/6/6,5 BABS L