

SAUTER FS 2-2KOY1

KERN

Pre-configured set consisting of the premium force gauge FS 2 and the measuring cell CO 200-Y1



Functions

IP protection - load cell	IP65
Peak function	✓
Memory function	✓
Statistic function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	selectable

Interface

Interfaces	USB-Device
------------	------------

Power Supply

Supplied power supply	Accu & Power supply
Power supply type	USB including power supply
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	UK
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Input voltage device / power [Max]	5 V, 1 A
Power socket for mains adapter	USB C
Battery / accumulator type	Li-Ion
Battery connection	2-pole tub connector
Battery capacity	2.400 mAh
Battery voltage	3,7 V
Battery - Number of cells	1
Battery - Construction	Inseparable connection of cells (pack)
Battery capacity (Wh)	8,88 Wh
Battery - Lithium content	720 mg
Rechargeable battery	3,7V, 2400mAh
Rechargeable battery operating time - backlight on	5 h
Rechargeable battery operating time - backlight off	8 h
Rechargeable battery charging time	8 h
Battery/Accu connected	fixed electrical connection, not insulated

Approval

CE mark	✓
---------	---

Category

Brand	Sauter
Product category	Force measurement
Product group	Force gauge set
Product family	FS OY1

Measuring System

Measuring range force [Max] (N)	2 kN
Readability force [d] (N)	0,4 N
Measuring head measuring frequency	1000 Hz
Directions of force	compression
Default unit	N
Number of platforms / channels	2

Display

Display type	TFT, color
Display resolution	320×480
Languages of the user interface	German English French Spanish Italian

Construction

Dimensions load cell (cylindrical)	20×12 mm
Material housing	plastic
Material display housing	plastic
Mounting - force dissipation	3 × threaded hole M3
Mounting - force application	Thrust piece (from customer side)

SAUTER FS 2-2KOY1

KERN

Pre-configured set consisting of the premium force gauge FS 2 and the measuring cell CO 200-Y1

Services (optional)

Article number for DAkkS calibration (compressive force)	963-262
--	---------

Packing & Shipping

Delivery time	3 d
Dimensions packaging (W×D×H)	320×290×180 mm
Shipping method	Parcel service
Net weight approx.	0,35 kg
Gross weight approx.	1,4 kg
Shipping weight	3,3 kg

Product information

GTIN/EAN number	4045761358232
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

