




**Part Number :** [2147700510](#)

**Product Description :** Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female Off-the-Shelf (OTS) Cable Assembly, Single Row, 1.0m Length, Tin (Sn) Plating, 5 Circuits, Black

**Series Number :** 214770

**Status :** Active

**Product Category :** Power and Signal Cable Assemblies



---

## Documents & Resources

### Drawings

[2147700510\\_sd.pdf](#)

### Specifications

[4000356554-000.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                          |
| China RoHS         |  |
| EU ELV             | Not Relevant                                                                          |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21                                                    |
| REACH SVHC         | Not Contained per D(2023)3788-DC (14 Jun 2023)                                        |
| EU RoHS            | Compliant per EU 2015/863                                                             |

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

|                        |                                                                                                                                               |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| Status                 | Active                                                                                                                                        |
| Category               | Power and Signal Cable Assemblies                                                                                                             |
| Series                 | 214770                                                                                                                                        |
| Description            | Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female Off-the-Shelf (OTS) Cable Assembly, Single Row, 1.0m Length, Tin (Sn) Plating, 5 Circuits, Black |
| Application            | Power, Wire-to-Board, Wire-to-Wire                                                                                                            |
| Assembly Configuration | Dual Ended Connectors                                                                                                                         |
| Connector to Connector | Micro-Fit 3.0 Both Ends                                                                                                                       |
| Product Name           | Micro-Fit 3.0                                                                                                                                 |
| Type                   | Overmolded Assembly                                                                                                                           |
| UPC                    | 193264653591                                                                                                                                  |

### Electrical

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 8.5A |
|-------------------------------|------|

### Physical

|                           |                 |
|---------------------------|-----------------|
| Cable Length              | 1.0m            |
| Circuits (Loaded)         | 5               |
| Circuits (maximum)        | 5               |
| Color - Resin             | Black           |
| Gender                    | Female-Female   |
| Lock to Mating Part       | Yes             |
| Material - Metal          | Phosphor Bronze |
| Material - Plating Mating | Tin             |
| Material - Resin          | Nylon           |
| Net Weight                | 94.491/g        |
| Number of Rows            | 1               |
| Overmolded                | Yes             |

|                             |                      |
|-----------------------------|----------------------|
| Pitch - Mating Interface    | 3.00mm               |
| Plating min - Mating        | 1.016µm              |
| Single Ended                | No                   |
| Termination Interface Style | Crimp or Compression |
| Wire/Cable Type             | UL 2464              |
| Wire Insulation Diameter    | 1.85mm max.          |
| Wire Size (AWG)             | 20                   |

---

## Mates With / Use With

### Mates with Part(s)

| Description                                                                   | Part Number   |
|-------------------------------------------------------------------------------|---------------|
| Micro-Fit 3.0 Single Row Plug Housings                                        | <u>43640</u>  |
| Micro-Fit TPA Single Row Plug Housings                                        | <u>200875</u> |
| Micro-Fit 3.0 Single Row Headers                                              | <u>43650</u>  |
| Micro-Fit 3.0 Male-to-Micro-Fit 3.0 Male Off-the-Shelf (OTS) Cable Assemblies | <u>214752</u> |
| Micro-Fit 3.0 Male-to-Pigtail Off-the-Shelf (OTS) Cable Assemblies            | <u>214753</u> |