

powerCON FXX

Interconnection cord set

Experience full compliance, unwavering reliability, and top-notch safety, all within your budget.

Neutrik Essential series Interconnection cords sets.



Features & Benefits

• Interconnection cord sets (local mains connectors – powerCON® FXX)	• High quality rubber cables or PVC jacketed power cables
• Cables with 1.5mm² and 2.5mm² conductor cross section	• powerCON® connectors (NAC3FXXA / NAC3FXXXB), certified according to the EN60320-1
• Ruggedized powerCON® connectors with Circuit Breaking Capacity (CBC)	• IP20
• Interconnection cord sets compliant to the IEC60799	• Attractive price / value ratio

Product safety

Electrical cables and connectors can pose risk to life and to the appliances. To guarantee the necessary level of protection. The requirements of the low voltage directive (LVD) must be met. The LVD requirements for the connector and cables are described in the **EN 60320** and **EN 60799** respectively. Compliance with these norms must be confirmed by CE declaration.

Essential series power cords

Neutrik Essential series power cords stand for full standard-compliance, unwavering reliability, and top-notch safety.

COMPLIANCE MATTERS. The new NEUTRIK powerCON blue / grey XX series connectors proudly carry the IEC-EN 60320-1 certification, complying with all required norms and standards. You can trust that your equipment is in good hands with NEUTRIK.

Full conformity of the power cord to the EU standards is confirmed by the CE declaration acc. to EN60799. The product [CE declaration](#) can be found in the Download area below.

SAFETY FIRST. At NEUTRIK, we prioritize your safety above all else. Our cables are rigorously tested and certified to ensure they meet the highest safety standards in the industry.

EXPERIENCE RELIABILITY. These cords guarantee the top-tier reliability. Embrace confidence with our ruggedized powerCON blue/grey XX connectors paired with high-quality cables.

EUROPEAN CRAFTSMANSHIP. Our cables are proudly produced in Europe, adhering to the highest manufacturing standards. European production guarantees precision, quality, and reliability that you can count on.


BEST PRICE. We prioritize high quality, unmatched safety standards, and cost efficiency! With our in-house connectors manufacturing and state-of-the-art, costeffective power cord production site, we bring you affordable prices that redefine value for money.

Article Variations


Article name	Details	Order code
NKPH01-A4A3-M0100	Cable: 1m H07RN-F3G1.5 (3x1.5mm ²); Connectors: powerCON FXXA / powerCON FXXB IP20	1036398
NKPH01-A4A3-M0150	Cable: 1.5m H07RN-F3G1.5 (3x1.5mm ²); Connectors: powerCON FXXA / powerCON FXXB IP20	1036399
NKPH01-A4A3-M0200	Cable: 2m H07RN-F3G1.5 (3x1.5mm ²); Connectors: powerCON FXXA / powerCON FXXB IP20	1036400
NKPH01-A4A3-M0300	Cable: 3m H07RN-F3G1.5 (3x1.5mm ²); Connectors: powerCON FXXA / powerCON FXXB IP20	1036401

NKPH01-A4A3-M0500	Cable: 5m H07RN-F3G1.5 (3x1.5mm ²); Connectors: powerCON FXXA / powerCON FXXB IP20	1036402
NKPH01-A4A3-M1000	Cable: 10m H07RN-F3G1.5 (3x1.5mm ²); Connectors: powerCON FXXA / powerCON FXXB IP20	1036403
NKPH02-A4A3-M0100	Cable: 1m H07RN-F3G2.5 (3x2.5mm ²); Connectors: powerCON FXXA / powerCON FXXB IP20	1036404
NKPH02-A4A3-M0150	Cable: 1.5m H07RN-F3G2.5 (3x2.5mm ²); Connectors: powerCON FXXA / powerCON FXXB IP20	1036405
NKPH02-A4A3-M0200	Cable: 2m H07RN-F3G2.5 (3x2.5mm ²); Connectors: powerCON FXXA / powerCON FXXB IP20	1036406
NKPH02-A4A3-M0300	Cable: 3m H07RN-F3G2.5 (3x2.5mm ²); Connectors: powerCON FXXA / powerCON FXXB IP20	1036407
NKPH02-A4A3-M0500	Cable: 5m H07RN-F3G2.5 (3x2.5mm ²); Connectors: powerCON FXXA / powerCON FXXB IP20	1036408
NKPH02-A4A3-M1000	Cable: 10m H07RN-F3G2.5 (3x2.5mm ²); Connectors: powerCON FXXA / powerCON FXXB IP20	1036409
NKPH11-A4A3-M0100	Cable: 1m H05VV-F3G1.5 (3x1.5mm ²); Connectors: powerCON FXXA / powerCON FXXB IP20	1036414
NKPH11-A4A3-M0150	Cable: 1.5m H05VV-F3G1.5 (3x1.5mm ²); Connectors: powerCON FXXA / powerCON FXXB IP20	1036415
NKPH11-A4A3-M0200	Cable: 2m H05VV-F3G1.5 (3x1.5mm ²); Connectors: powerCON FXXA / powerCON FXXB IP20	1036416
NKPH11-A4A3-M0300	Cable: 3m H05VV-F3G1.5 (3x1.5mm ²); Connectors: powerCON FXXA / powerCON FXXB IP20	1036417
NKPH11-A4A3-M0500	Cable: 5m H05VV-F3G1.5 (3x1.5mm ²); Connectors: powerCON FXXA / powerCON FXXB IP20	1036418
NKPH11-A4A3-M1000	Cable: 10m H05VV-F3G1.5 (3x1.5mm ²); Connectors: powerCON FXXA / powerCON FXXB IP20	1036419

INTERCONNECTION CORD SET, RUBBER CABLE (NKPH01/02-A4A3)



Partnumber Breakdown



Mating scenario

APPLIANCE INLET

A type (color coding blue)

