


Datasheet

Manufacturer Part No.: T23C003



Crimp connector assortment 500 pcs set

Fork connectors, ring terminals, blade receptacles, flat plugs, round plugs, round plug sleeves



This crimp connectors guarantee optimal results in conjunction with fitting crimping tools. The assortment includes the most common parts used in practice. It is especially suitable for hobbyists, craftsmen, field service, service workshops, electronics technicians and laboratory needs.
Must be used only by qualified electricians!

Content	Description	Material	Cross section
25 pcs	Fork connector red, holeØ 3.1 mm	Copper, tin plated	0.5...1.5 mm ²
25 pcs	Fork connector blue, holeØ 4.1 mm	Copper, tin plated	0.5...1.5 mm ²
20 pcs	Fork connector red, holeØ 5.2 mm	Copper, tin plated	1.5...2.5 mm ²
25 pcs	Ring terminal red, holeØ 3.1 mm	Copper, tin plated	0.5...1.5 mm ²
25 pcs	Ring terminal blue, holeØ 4.1 mm	Copper, tin plated	0.5...1.5 mm ²
20 pcs	Ring terminal red, holeØ 5.2 mm	Copper, tin plated	1.5...2.5 mm ²
25 pcs	Fork connector red, holeØ 3.1 mm	Copper, tin plated	0.5...1.5 mm ²
25 pcs	Fork connector blue, holeØ 4.1 mm	Copper, tin plated	0.5...1.5 mm ²
20 pcs	Fork connector red, holeØ 5.2 mm	Copper, tin plated	1.5...2.5 mm ²
25 pcs	Ring terminal red, holeØ 3.1 mm	Copper, tin plated	0.5...1.5 mm ²
25 pcs	Ring terminal blue, holeØ 4.1 mm	Copper, tin plated	0.5...1.5 mm ²
20 pcs	Ring terminal red, holeØ 5.2 mm	Copper, tin plated	1.5...2.5 mm ²
25 pcs	Blade receptacles red, 2.8 mm	Copper, tin plated	0.5...1.5 mm ²
25 pcs	Blade receptacles blue, 4.8 mm	Copper, tin plated	0.5...1.5 mm ²
20 pcs	Blade receptacles yellow, 6.3 mm	Copper, tin plated	1.5...2.5 mm ²
25 pcs	Flat plug red, 2.8 mm	Copper, tin plated	0.5...1.5 mm ²
25 pcs	Flat plug blue, 4.8 mm	Copper, tin plated	0.5...1.5 mm ²
20 pcs	Flat plug yellow, 6.3 mm	Copper, tin plated	1.5...2.5 mm ²
20 pcs	Round plug red, Ø 4 mm	Copper, tin plated	0.5...1.5 mm ²
20 pcs	Round plug sleeve red, Ø 4 mm	Copper, tin plated	1.5...2.5 mm ²
20 pcs	Round plug blue, Ø 4 mm	Copper, tin plated	0.5...1.5 mm ²
20 pcs	Round plug sleeve blue, Ø 4 mm	Copper, tin plated	1.5...2.5 mm ²