



Einhell

CLASSIC



Cordless Light

TC-CL 18/350 Li - Solo

Item No.: 4514175

Ident No.: 21013

Bar Code: 4006825673371

The Einhell cordless lamp TC-CL 18/350 Li – Solo is a member of the Power X-Change family and a reliable aid when working in poorly lit areas. The powerful LED outputs 350 lm and 7000 K and provides optimal illumination with daylight-like light colour at a distance of up to 30 m. The swivelling light head offers maximum flexibility in use. The lightweight cordless lamp is ideal for mobile use and is particularly handy thanks to its softgrip. With the help of the integrated fastening eye, the lamp can be easily hung or stored in a space-saving manner. The product does not include a battery or charger.

Features & Benefits



- Part of the Power X-Change family, 1 x 18V battery required
- High-quality, bright LED with a 350 lumens of luminous flux
- 7000 K for daylight-like, bright light conditions
- Ideal for illuminating distances of up to 30 m
- High flexibility thanks to the swivelling light head
- Slim, lightweight design for flexible use
- Ergonomic handle with softgrip
- Simple storage with fastening eyelet
- Comes without battery or charger (sold separately)

Technical Data

- | | |
|---|----------------|
| - Quantity of LED | 1 Pieces |
| - Luminous flux max. | 350 lm |
| - Luminous colour | 7000 K |
| - Number of brightness adjustment steps | Not adjustable |

Logistic Data

- | | |
|--------------------------------------|----------------------|
| - Product weight | 0.48 |
| - Gross weight single packaging | 0.88 |
| - Dimensions single packaging | 252 x 100 x 160 mm |
| - Pieces per export carton | 8 Pieces |
| - Gross weight export carton | 7.2 kg |
| - Dimensions export carton | 440 x 270 x 345 mm |
| - Container quantity (20"/40"/40"HC) | 5464 11320 13272 |



Available as special accessories



4-6 Ah Multi-Ah Power X-Change Plus Battery
Item No.: 4511502
Bar Code: 4006825644210



4,0 Ah Power X-Change Battery
Item No.: 4511396
Bar Code: 4006825610376
Einhell Accessory



2x2 Power X-Quattrocharger 4A Charger
Item No.: 4512102
Bar Code: 4006825649536
Einhell Accessory



Power X-Twincharger 3A Charger
Item No.: 4512069
Bar Code: 4006825629729
Einhell Accessory



Power X-Car Charger 3A Charger
Item No.: 4512113
Bar Code: 4006825655377
Einhell Accessory



2x 18V 5,2Ah PXC-Twinpack Battery
Item No.: 4511526
Bar Code: 4006825656695
Einhell Accessory



2x18V 4,0Ah PXC-Twinpack CB A1 Battery
Item No.: 4511489
Bar Code: 4006825638578



18V 5-8Ah Multi-Ah PXC Plus Battery
Item No.: 4511600
Bar Code: 4006825665055
Einhell Accessory



18V 4,0Ah Power-X-Change Plus Battery
Item No.: 4511553
Bar Code: 4006825660869
Einhell Accessory



2,0 Ah Power X-Change Battery
Item No.: 4511395
Bar Code: 4006825610369
Einhell Accessory



18V 2,5Ah PXC Starter Kit PXC-Starter-Kit
Item No.: 4512097
Bar Code: 4006825646962
Einhell Accessory



18V 4,0Ah PXC Starter Kit A1 PXC-Starter-Kit
Item No.: 4512042
Bar Code: 4006825613704
Einhell Accessory



Power X-Fastcharger 4A Charger
Item No.: 4512103
Bar Code: 4006825650228
Einhell Accessory



18V 3,0 Ah Power-X-Change 1 Battery
Item No.: 4511341
Bar Code: 4006825590593
Einhell Accessory



2x 4,0Ah & Twincharger Kit 1 PXC-Starter-Kit
Item No.: 4512112
Bar Code: 4006825655766
Einhell Accessory



5,2Ah & 4A Fastcharger PXC-Starter-Kit
Item No.: 4512114
Bar Code: 4006825656787
Einhell Accessory



3,0 Ah Power X-Change Plus Battery
Item No.: 4511501
Bar Code: 4006825644197
Einhell Accessory



5,2 Ah Power X-Change Plus Battery
Item No.: 4511437
Bar Code: 4006825616606
Einhell Accessory



18V 2,0Ah PXC Starter Kit PXC-Starter-Kit
Item No.: 4512040
Bar Code: 4006825613681
Einhell Accessory

Battery-Running-Times



shining¹
(h)

One Battery for All

1.5 Ah	6
2.0 Ah	7.5
2.5 Ah	10
3.0 Ah	11
4.0 Ah	15
5.2 Ah	20
6.0 Ah	23
8.0 Ah	30

Test setup:

1) Light on