CT120 EX Reverse ARGB Sync PC Cooling Fan

3 Pack

*Requires motherboard sync for ARGB lighting effect

Thermaltake CT120/140 EX Reverse ARGB Sync PC Cooling Fan

• Features

CT120 EX Reverse

- Reversed blade fan enables airflow from rear to front while fully showing lighting effects
- MagForce 2.0, a new Magnetic Connection Design for optimized fan daisy-chaining
- Connect multiple fans with only one cable
- 9 addressable LEDs controlled by 5V motherboard sync software
- Specifically tuned fan blade with greater airflow and static pressure
- Optimized hydraulic bearing for reliable and silent operation
- Anti-vibration Mounting System emb[illegible]

3 Pack

• Specification

Part Number	CL-F192-PL12SW-A (Black) CL-F194-PL12SW-A (White) CL-F198-PL12BU-A (Hydrangea Blue) CL-F198-PL12MG-A (Matcha Green) CL-F223-PL12BB-A (Bumblebee) CL-F224-PL12GS-A (Gravel Sand) CL-F225-PL12PK-A (Pink) CL-F226-PL12RG-A (Racing Green)
Fan Dimension	120 x 120 x 25 mm
Started Voltage	5 V
Rated Voltage	12 V & 5 V
Rated Current	0.19 A & 0.32 A (one fan)
Power Input	2.28 W & 1.6 W (one fan)
Fan Speed	PWM 500 ~ 2000 R.P.M
Air Pressure.	1.87 mm-H2O
Air Flow.	65.82 CFM
Acoustical Noise.	31.2 dB-A
Bearing Type	Hydraulic Bearing
Life Expectation	40,000 hrs, 25℃
Interface	4 Pin - PWM 12 V 3 Pin - ARGB Sync 5 V
Included Items	Fan x 3, Cable x 3

*Requires motherboard sync for ARGB lighting effect

•Angle View

CT120 EX Reverse Black

Front view

Back view



Side view

MagForce 2.0 Cable

Parts

(M3 screw for radiator x 12, T5 fan screw x 12, MagForce 2.0 cable x 3)

•Angle View

CT120 EX Reverse White

Front view

Back view

Side view

MagForce 2.0 Cable

Parts

(M3 screw for radiator x 12, T5 fan screw x 12, MagForce 2.0 cable x 3)

•Angle View

CT120 EX Reverse Hydrangea Blue

Front view

Back view

Side view

MagForce 2.0 Cable



Parts

(M3 screw for radiator x 12, T5 fan screw x 12, MagForce 2.0 cable x 3)

•Angle View

CT120 EX Reverse Matcha Green

Front view

Back view

Side view

MagForce 2.0 Cable



Parts

(M3 screw for radiator x 12, T5 fan screw x 12, MagForce 2.0 cable x 3)

•Angle View

CT120 EX Reverse Bumblebee

Front view

Back view

Side view

MagForce 2.0 Cable



Parts

(M3 screw for radiator x 12, T5 fan screw x 12, MagForce 2.0 cable x 3)

•Angle View

CT120 EX Reverse Gravel Sand

Front view

Back view

Side view

MagForce 2.0 Cable



Parts

(M3 screw for radiator x 12, T5 fan screw x 12, MagForce 2.0 cable x 3)

•Angle View

CT120 EX Reverse Pink

Front view

Back view

Side view

MagForce 2.0 Cable

Parts

(M3 screw for radiator x 12, T5 fan screw x 12, MagForce 2.0 cable x 3)

•Angle View

CT120 EX Reverse Racing Green

Front view

Back view



Side view

MagForce 2.0 Cable



Parts

(M3 screw for radiator x 12, T5 fan screw x 12, MagForce 2.0 cable x 3)

Thermaltake CT120/140 EX Reverse ARGB Sync PC Cooling Fan

- **Detail Features**



MagForce 2.0 Design

Optimized fan daisy-chaining for better cable management

User Friendly Interface

Connect multiple fans with only one cable

Application

To provide the best cooling solution inside your chassis

•5V Sync

Support ASUS、MSI、GIGABYTE and ASROCK 5V ARGB motherboard sync.

*Caution: the motherboard signal connector only supports 5V header.

Aura Addressable Header

Digital Pin Header

JRAINBOW Header

Addressable RGB LED Header

CT120 EX Reverse ARGB Sync PC Cooling Fan

3 Pack

AURA SYNC · RGB FUSION 2.0 GIGABYTE · msi MYSTIC LIGHT SYNC

thermaltake

*Requires motherboard sync for ARGB lighting effect

CT140 EX Reverse ARGB Sync PC Cooling Fan

3 Pack

AURA SYNC · RGB FUSION 2.0 GIGABYTE · msi MYSTIC LIGHT SYNC

thermaltake

*Requires motherboard sync for ARGB lighting effect

Thermaltake CT120/140 EX Reverse ARGB Sync PC Cooling Fan

• Features

CT140 EX Reverse

- Reversed blade fan enables airflow from rear to front while fully showing lighting effects
- MagForce 2.0, a new Magnetic Connection Design for optimized fan daisy-chaining
- Connect multiple fans with only one cable
- 9 addressable LEDs controlled by 5V motherboard sync software
- Specifically tuned fan blade with greater airflow and static pressure
- Optimized hydraulic bearing for reliable and silent operation
- Anti-vibration Mounting System embedded

• Specification

3 Pack

Part Number	CL-F193-PL14SW-A (Black) CL-F195-PL14SW-A (White) CL-F199-PL14BU-A (Hydrangea Blue) CL-F199-PL14MG-A (Matcha Green) CL-F227-PL14BB-A (Bumblebee) CL-F228-PL14GS-A (Gravel Sand) CL-F229-PL14PK-A (Pink) CL-F230-PL14RG-A (Racing Green)
Fan Dimension	140 x 140 x 25 mm
Started Voltage	5 V
Rated Voltage	12 V & 5 V
Rated Current	0.25 A & 0.32 A (one fan)
Power Input	3 W & 1.6 W (one fan)
Fan Speed	PWM 500 ~ 1800 R.P.M
Air Pressure.	2.54 mm-H2O
Air Flow.	94.95 CFM
Acoustical Noise.	32.8 dB-A
Bearing Type	Hydraulic Bearing
Life Expectation	40,000 hrs, 25℃
Interface	4 Pin - PWM 12 V 3 Pin - ARGB Sync 5 V
Included Items	Fan x 3, Cable x 3

*Requires motherboard sync for ARGB lighting effect

•Angle View

CT140 EX Reverse Black

Front view

Back view



Side view

MagForce 2.0 Cable

Parts

(M3 screw for radiator x 12, T5 fan screw x 12, MagForce 2.0 cable x 3)

•Angle View

CT140 EX Reverse White

Front view

Back view

Side view

MagForce 2.0 Cable

Parts

(M3 screw for radiator x 12, T5 fan screw x 12, MagForce 2.0 cable x 3)

•Angle View

CT140 EX Reverse Hydrangea Blue

Front view



Back view

Side view

MagForce 2.0 Cable



Parts

(M3 screw for radiator x 12, T5 fan screw x 12, MagForce 2.0 cable x 3)

•Angle View

CT140 EX Reverse Matcha Green

Front view

Back view

Side view

MagForce 2.0 Cable



Parts
(M3 screw for radiator x 12, T5 fan screw x 12, MagForce 2.0 cable x 3)

•Angle View

CT140 EX Reverse Bumblebee

Front view

Back view

Side view

MagForce 2.0 Cable



Parts

(M3 screw for radiator x 12, T5 fan screw x 12, MagForce 2.0 cable x 3)

•Angle View

CT140 EX Reverse Gravel Sand

Front view

Back view

Side view

MagForce 2.0 Cable



Parts

(M3 screw for radiator x 12, T5 fan screw x 12, MagForce 2.0 cable x 3)

•Angle View

CT140 EX Reverse Pink

Front view

Back view

Side view

MagForce 2.0 Cable

Parts

(M3 screw for radiator x 12, T5 fan screw x 12, MagForce 2.0 cable x 3)

•Angle View

CT140 EX Reverse Racing Green

Front view

Back view



Side view

MagForce 2.0 Cable



Parts

(M3 screw for radiator x 12, T5 fan screw x 12, MagForce 2.0 cable x 3)

Thermaltake CT120/140 EX Reverse ARGB Sync PC Cooling Fan

- **Detail Features**



MagForce 2.0 Design

Optimized fan daisy-chaining for better cable management

User Friendly Interface

Connect multiple fans with only one cable

Application

To provide the best cooling solution inside your chassis

•5V Sync

Support ASUS、MSI、GIGABYTE and ASROCK 5V ARGB motherboard sync.

*Caution: the motherboard signal connector only supports 5V header.

Aura Addressable Header

Digital Pin Header

JRAINBOW Header

Addressable RGB LED Header

CT140 EX Reverse ARGB Sync PC Cooling Fan

3 Pack

AURA SYNC · RGB FUSION 2.0 GIGABYTE · msi MYSTIC LIGHT SYNC

thermaltake

*Requires motherboard sync for ARGB lighting effect