




**Part Number :** [2162731031](#)  
**Product Description :** SL Male-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Positive Lock, Single Row, 100.00mm Length, Tin (Sn) Plating, 3 Circuits, Black  
**Series Number :** 216273  
**Status :** Active  
**Product Category :** Power and Signal Cable Assemblies



## Documents & Resources

**Drawings**  
[2162731031\\_sd.pdf](#)

**3D Models and Design Files**  
[2162731031\\_stp.zip](#)

## Product Environment Compliance

### Compliance

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                          |
| China RoHS         |  |
| EU ELV             | Not Relevant                                                                          |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21                                                    |
| REACH SVHC         | Not Contained per D(2024)6225-DC (07 Nov 2024)                                        |
| EU RoHS            | Compliant per EU 2015/863                                                             |

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

|                        |                                                                                                                                        |
|------------------------|----------------------------------------------------------------------------------------------------------------------------------------|
| Status                 | Active                                                                                                                                 |
| Category               | Power and Signal Cable Assemblies                                                                                                      |
| Series                 | 216273                                                                                                                                 |
| Description            | SL Male-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Positive Lock, Single Row, 100.00mm Length, Tin (Sn) Plating, 3 Circuits, Black |
| Application            | Signal, Wire-to-Wire                                                                                                                   |
| Assembly Configuration | Single Ended Connector                                                                                                                 |
| Connector to Connector | SL-to-Pigtail                                                                                                                          |
| Product Name           | SL                                                                                                                                     |
| Type                   | Discrete Wire Assembly                                                                                                                 |
| UPC                    | 193264731503                                                                                                                           |

### Electrical

|                               |            |
|-------------------------------|------------|
| Current - Maximum per Contact | 3.0A       |
| Voltage - Maximum             | 600V AC/DC |

### Physical

|                                |                 |
|--------------------------------|-----------------|
| Cable Length                   | 100.00mm        |
| Circuits (Loaded)              | 3               |
| Circuits (maximum)             | 3               |
| Color - Resin                  | Black           |
| Gender                         | Male-Pigtail    |
| Lock to Mating Part            | Yes             |
| Material - Metal               | Phosphor Bronze |
| Material - Plating Mating      | Tin             |
| Material - Plating Termination | Tin             |
| Material - Resin               | Polyester Alloy |
| Net Weight                     | 2.598/g         |

|                             |                      |
|-----------------------------|----------------------|
| Number of Rows              | 1                    |
| Overmolded                  | No                   |
| Packaging Type              | Bag                  |
| Pitch - Mating Interface    | 2.54mm               |
| Single Ended                | Yes                  |
| Termination Interface Style | Crimp or Compression |
| Wire/Cable Type             | UL 11028             |
| Wire Insulation Diameter    | 1.63mm max.          |
| Wire Size (AWG)             | 22                   |

---

## Mates With / Use With

### Mates with Part(s)

| Description                                                       | Part Number  |
|-------------------------------------------------------------------|--------------|
| SL Single Row Crimp Housings and CPA Retainers                    | <u>70066</u> |
| SL Single Row Female Insulation Displacement Connector Assemblies | <u>70400</u> |
| SL Single Row Female Receptacles                                  | <u>70430</u> |