

PRODUCT

7 Inch Antistatic Plastic Reels

TECHNICAL DATASHEET



DESCRIPTION



One piece 7" plastic reels injection moulded using antistatic high impact polystyrene. Provides excellent protection when shipping tiny components packaged in carrier tape.

SHELF LIFE AND STORAGE

Reels should be stored in original packaging in a climate-controlled environment where the temperature ranges from 20°C - 30°C (68°F - 86°F) with a relative humidity of 50%±10%

FEATURES

- Available in variety of widths
- Hub diameter 60±0.20mm
- EIA standard carrier tape widths



PROPERTIES	TYPICAL VALUE	TEST METHOD
Type	One Piece	-
Material	High Impact Polystyrene	-
Surface Resistance	$\leq 10^{11} \Omega$	ASTM-D257

To request a quotation or for more information, please call **+44 (0)1473 836200**
email info@antistat.co.uk or visit www.antistat.co.uk

IMPORTANT: This data sheet and its contents (the "Information") belong to Antistat or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Antistat assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Antistat was aware of the possibility of such loss or damage arising) is excluded. © 2025 Antistat.

PRODUCT CODE	REEL SIZE	HUB DIAMETER	PACKAGE
029-0043	7" x 8mm	60±0.20mm	318 pcs/case
029-0044	7" x 12mm	60±0.20mm	228 pcs/case
029-0045	7" x 16mm	60±0.20mm	180 pcs/case
029-0046	7" x 24mm	60±0.20mm	126 pcs/case

To request a quotation or for more information, please call **+44 (0)1473 836200**
email info@antistat.co.uk or visit www.antistat.co.uk

IMPORTANT: This data sheet and its contents (the "Information") belong to Antistat or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Antistat assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Antistat was aware of the possibility of such loss or damage arising) is excluded. © 2025 Antistat.