

6220 0554	DATA SHEET
Valid from: 17.05.2018	Cable Trolley Steel Wire

The Cable Trolley System is designed for a steel wire and is available as flat- and round cable system
The fastening components are suitable for both systems.

Material:

Metal Parts

Steel, galvanized

Bodies

Polyamide

Clamps

Polyamide

Technical features

Temperature range

-40°C up to +120°C

Max. Load

6kg / Cable Trolley

Description:

- The Cable Trolley System is available as flat- and round cable system.
- The fastening components are suitable for both systems.


Additional product data:

ETIM 5.0 Class-ID: EC002935

ETIM 5.0 Class-Description: Accessories for Cable Trolley Systems








Notes:

- The bending radius corresponds to a permanent installation.








1. Tension bracket
2. Fixed plate cable clamp
3. Tension screw
4. Cable Trolley
5. Steel wire 6mm
6. Towing trolley
7. Cable clamp, adjustable

6220 0554	DATA SHEET
Valid from: 17.05.2018	Cable Trolley Steel Wire

Description Part No.	Max. Cable measure mm	Measu res mm	Weight kg	Image	Drawing
Cable Trolley Flat Cable					
Cable Trolley with 2 wheels for flat cable Part No. 62200554	15 x 44	L: 85 D: 50 B1: 69 B2: 44	0,10		
Mounting plate for end clamp Part No. 62200555	15 x 44	L: 80 D: 80 B1: 80 B2: 54	0,22		
Towing trolley Part No. 62200556	15 x 44	L: 410	1,22		
Cable Trolley Round Cable					
Towing trolley with 2 wheels and ball joint Part No. 62200557		L: 85	0,10		
Mounting plate for end clamp Part No. 62200559			0,17		
Towing trolley Part No. 62200558			1,18		

6220 0554	DATA SHEET
Valid from: 17.05.2018	Cable Trolley Steel Wire

Description	Max. Cable measure mm	Measures mm	Weight kg	Image	Drawing
Part No.					
Cable clamp round 10 - 16mm Part No. 62200437	d = 10 - 16	L = 70 R = 80	0,04		
Cable clamp round 17 - 25mm Part No. 62200438	d = 17 - 25	L = 100 R = 125	0,06		
Cable clamp round 26 - 36mm Part No. 62200439	d = 26 - 36	L = 140 R = 160	0,12		
Attachments Cable Trolleys Round- and Flat Cable					
Tension bracket Part No. 62200561		L = 440	2,1		
Tension screw Part No. 62200562			0,25		
Steel wire Part No. 62200565		D = 6	0,12		
Steel wire PVC coated Part No. 62200563		D = 6	0,10		

Footnote:

The images are no scaled and detailed images from the products.