



Part Number : [192150048](#)  
Product Description : VersaKrimp Butt Splice  
for 2/0 AWG Wire  
Series Number : 19215  
Status : Active  
Product Category : Splices  
Engineering Number : J-388



Documents & Resources

Drawings  
[192150048\\_sd.pdf](#)

Specifications  
[PS-19902-011-001.pdf](#)  
[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                          |
| China RoHS         |  |
| EU ELV             | Not Relevant                                                                          |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                                                        |
| REACH SVHC         | Not Contained per D(2024)6225-DC<br>(07 Nov 2024)                                     |
| EU RoHS            | Compliant per EU 2015/863                                                             |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

|              |                                         |
|--------------|-----------------------------------------|
| Status       | Active                                  |
| Category     | Splices                                 |
| Series       | 19215                                   |
| Description  | VersaKrimp Butt Splice for 2/0 AWG Wire |
| Product Name | Butt,VersaKrimp                         |
| UPC          | 800755062687                            |

#### Physical

|                                |                 |
|--------------------------------|-----------------|
| Barrel Type                    | Closed - Brazed |
| Insulation                     | None            |
| Material - Metal               | Copper          |
| Material - Plating Mating      | Tin             |
| Material - Plating Termination | Tin             |
| Net Weight                     | 31.253/g        |
| Packaging Type                 | Bag             |
| Wire Size (AWG)                | 2/0             |

---

### Application Tooling

#### Global

|                                                                                                           |                  |
|-----------------------------------------------------------------------------------------------------------|------------------|
| Description                                                                                               | Part Number      |
| Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices | <u>192860117</u> |
| Die Set (Large) for the HHLS Hydraulic Crimper                                                            | <u>192900012</u> |
| Manual Tool for Crimping Non-insulated 8 AWG thru 4/0 Terminals                                           | <u>192940008</u> |

|                                                                                                                   |                  |
|-------------------------------------------------------------------------------------------------------------------|------------------|
| Square "Din" Style Die Set for BCL and VersaKrimp Un-insulated Ring Tongue Terminals and Splices, 1/0 and 2/0 AWG | <u>640038070</u> |
| Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices                             | <u>638162000</u> |

---

This document was generated on Mar 03, 2025