



Part Number : [02096106](#)
Product Description : 2.36mm Diameter,
Standard .093" Pin and Socket Crimp
Terminal, Series 1190, Male, with Gold (Au)
Plated Brass Contact, 20-14 AWG, Bag
Series Number : 1190
Status : Active
Product Category : Crimp Terminals
Engineering Number : 1190-(550)L
Packaging Alternative : 02096100 (Reel)



Documents & Resources

Drawings
[002096106_sd.pdf](#)
[PK-1190-003-001.pdf](#)

Specifications
[PK-1190-001-001.pdf](#)
[PS-02-09-001.pdf](#)
[11890000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	1190
Description	2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1190, Male, with Gold (Au) Plated Brass Contact, 20-14 AWG, Bag
Application	Power, Wire-to-Wire
Product Name	Standard .093"
UPC	800753615465

Physical

Durability (mating cycles max)	25
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.414/g
Packaging Type	Bag
Plating min - Mating	0.381µm
Plating min - Termination	0.254µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.65-4.06mm
Wire Size (AWG)	14, 16, 18, 20
Wire Size mm²	N/A

Application Tooling

Global

Description	Part Number
Insertion Tool for Standard .093" Pin and Socket Terminals	<u>11020003</u>
Extraction Tool for Standard .093" Pin and Socket Terminals	<u>11030006</u>
ServiceGrade Hand Crimp Tool for Field Repair Only, 24-14 AWG	<u>638111000</u>
PremiumGrade Hand Crimp Tool for Standard .093" and .125" Pin and Socket Terminals	<u>638191100</u>
Extractor Tool for .093 and HCS-125 Product Series	<u>638240200</u>