

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5050060810

Status:

Active

Overview:


SlimStack™ 0.40mm Pitch Board-to-Board Connectors

Description:

SlimStack Hybrid Power SMT Board-to-Board Plug, 0.40mm Pitch, 0.75mm Height, 4 Power, 4 Signal Contacts

Replacement Part Number:

http://www.molex.com/molex/products/listview.jsp?channel=Products&sType=p&query=5050060812505006-0812 (drop-in)



Series image - Reference only

Documents:	
3D Model	Application Specification AS-505004-001-001 (PDF)
Drawing (PDF)	Packaging Specification SPK-505006-001-001 (PDF)
Product Specification PS-505004-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	505006
Application	Board-to-Board
Overview	SlimStack™ 0.40mm Pitch Board-to-Board Connectors
Product Name	SlimStack
Replacement Part Number	505006-0812 (drop-in)
Series Name	Battery
UPC	887191595085
Physical	
(p)ower-(s)ignal Configuration	4p - 4s
Breakaway	No
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Durability (mating cycles max)	10
Glow-Wire Capable	No
Lock to Mating Part	Yes
Mated Height	0.75mm
Mated Width	2.50mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Gold over Nickel
Material - Resin	Liquid Crystal Polymer
Net Weight	5.410/mg
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.40mm
Polarized to Mating Part	No
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	0.3A, 3.0A
Voltage - Maximum	50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/61/2018 (27 June 2018)	
Halogen-Free	
Status	
Low-Halogen	
Need more information on product environmental compliance?	
Email productcompliance@molex.com	
Please visit the Contact Us section for any non-product compliance questions.	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

505006 Series

Mates With

505004 0.40mm Pitch SlimStack Board-to-Board Battery Receptacle

Application Specification	AS-505004-001-001
Packaging Specification	SPK-505006-001-001
Product Specification	PS-505004-001-001
Sales Drawing	SD-505006-001, SD-505006-002

This document was generated on 08/28/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION