




**Part Number :** [732306260](#)  
**Product Description :** MCX Right-Angle Plug-to-I-PEX MHF 4L LK Plug, 1.37mm Cable Diameter, 305.80mm Cable Length, 50 Ohms  
**Series Number :** 73230  
**Status :** Active  
**Product Category :** RF Cable Assemblies



## Documents & Resources

**Drawings**  
[732306260\\_sd.pdf](#)

## Product Environment Compliance

### Compliance

|                    |                                               |
|--------------------|-----------------------------------------------|
| GADSL/IMDS         | Not Relevant                                  |
| China RoHS         | Not Reviewed per SJ/T 11365-2006              |
| EU ELV             | Not Relevant                                  |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21               |
| REACH SVHC         | Not Reviewed per D(2024)6225-DC (07 Nov 2024) |
| EU RoHS            | Compliant with Exemption 6(c) per EU 2015/863 |

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

## Part Details

### General

|                        |                                                                                                              |
|------------------------|--------------------------------------------------------------------------------------------------------------|
| Status                 | Active                                                                                                       |
| Category               | RF Cable Assemblies                                                                                          |
| Series                 | 73230                                                                                                        |
| Description            | MCX Right-Angle Plug-to-I-PEX MHF<br>4L LK Plug, 1.37mm Cable<br>Diameter, 305.80mm Cable Length,<br>50 Ohms |
| Assembly Configuration | Dual Ended Connectors                                                                                        |
| Connector to Connector | MCX-to-I-PEX MHF                                                                                             |
| Product Name           | I-PEX MHF,MCX                                                                                                |
| Type                   | RF Cable Assembly                                                                                            |
| UPC                    | 196823189203                                                                                                 |

### Electrical

|           |     |
|-----------|-----|
| Impedance | 50Ω |
|-----------|-----|

### Physical

|                           |                 |
|---------------------------|-----------------|
| Cable Length              | 305.80mm        |
| Gender                    | Plug/Plug       |
| Material - Metal          | Brass           |
| Material - Plating Mating | Gold            |
| Net Weight                | 4.000/g         |
| Packaging Type            | Bag             |
| Single Ended              | No              |
| Wire/Cable Type           | 1.37mm, Coaxial |