



Minus Pad Basic



Minus Pad Advance



Minus Pad Pro



High Performance Cooling Solutions

With the new Minus Pad Basic, Advance, and Pro series, Thermal Grizzly is expanding its thermal pad portfolio with a range of advanced pads. Based on the proven Minus Pad 8, these new pads have been specifically enhanced to significantly improve thermal conductivity, compressibility, while lowering the price at the same time.


- Minus Pad Basic: Good thermal conductivity, good compressibility, and an excellent price-performance ratio.
- Minus Pad Advance: Even better thermal conductivity and higher compressibility.
- Minus Pad Pro: Extremely high thermal conductivity and outstanding compressibility – at a slightly higher price.

The electrically non-conductive pads in the Basic, Advance, and Pro series are ideal for SSDs, graphics card coolers, GPU water blocks, and electronic components such as voltage regulators and RAM. They are each available in 100 × 100 mm and 120 × 20 mm sizes, with thicknesses of 0.5 mm, 1.0 mm, 1.5 mm, 2.0 mm, and 3.0 mm.


Short Information

- Easy to use
- Available in common sizes
- Good to very good compressibility and thermal conductivity
- Electrically non-conductive


Minus Pad Basic




Minus Pad Advance




Minus Pad Pro



minus pad 8



minus pad extreme



Technical Data

Colour: Grey

Products:	Item Number:	EAN Code:	Pad size:	Content:	PU:
Minus Pad Basic	TG-MP-B-100-100-05-2	4260711991455	100x 100x 0,5 mm	2 Pcs.	15 Pcs.
	TG-MP-B-100-100-10-2	4260711991462	100x 100x 1,0 mm	2 Pcs.	10 Pcs.
	TG-MP-B-100-100-15-2	4260711991479	100x 100x 1,5 mm	2 Pcs.	10 Pcs.
	TG-MP-B-100-100-20-2	4260711991486	100x 100x 2,0 mm	2 Pcs.	5 Pcs.
	TG-MP-B-120-20-05-4	4260711991493	120x 20x 0,5 mm	4 Pcs.	20 Pcs.
	TG-MP-B-120-20-10-4	4260711991509	120x 20x 1,0 mm	4 Pcs.	15 Pcs.
	TG-MP-B-120-20-15-4	4260711991516	120x 20x 1,5 mm	4 Pcs.	10 Pcs.
	TG-MP-B-120-20-20-4	4260711991523	120x 20x 2,0 mm	4 Pcs.	10 Pcs.
	TG-MP-B-120-20-30-4	4260711991530	120x 20x 3,0 mm	4 Pcs.	5 Pcs.
Minus Pad Advance	TG-MP-A-100-100-05-2	4260711991363	100x 100x 0,5 mm	2 Pcs.	15 Pcs.
	TG-MP-A-100-100-15-2	4260711991370	100x 100x 1,0 mm	2 Pcs.	10 Pcs.
	TG-MP-A-100-100-10-2	4260711991387	100x 100x 1,5 mm	2 Pcs.	10 Pcs.
	TG-MP-A-100-100-20-2	4260711991394	100x 100x 2,0 mm	2 Pcs.	5 Pcs.
	TG-MP-A-120-20-05-4	4260711991400	120x 20x 0,5 mm	4 Pcs.	20 Pcs.
	TG-MP-A-120-20-10-4	4260711991417	120x 20x 1,0 mm	4 Pcs.	15 Pcs.
	TG-MP-A-120-20-15-4	4260711991424	120x 20x 1,5 mm	4 Pcs.	10 Pcs.
	TG-MP-A-120-20-20-4	4260711991431	120x 20x 2,0 mm	4 Pcs.	10 Pcs.
	TG-MP-A-120-20-30-4	4260711991448	120x 20x 3,0 mm	4 Pcs.	5 Pcs.
Minus Pad Pro	TG-MP-P-100-100-05	4260711991547	100x 100x 0,5 mm	1 Pcs.	20 Pcs.
	TG-MP-P-100-100-10	4260711991561	100x 100x 1,0 mm	1 Pcs.	15 Pcs.
	TG-MP-P-100-100-15	4260711991554	100x 100x 1,5 mm	1 Pcs.	20 Pcs.
	TG-MP-P-100-100-20	4260711991578	100x 100x 2,0 mm	1 Pcs.	15 Pcs.
	TG-MP-P-120-20-05-2	4260711991585	120x 20x 0,5 mm	2 Pcs.	40 Pcs.
	TG-MP-P-120-20-10-2	4260711991592	120x 20x 1,0 mm	2 Pcs.	30 Pcs.
	TG-MP-P-120-20-15-2	4260711991608	120x 20x 1,5 mm	2 Pcs.	25 Pcs.
	TG-MP-P-120-20-20-2	4260711991615	120x 20x 2,0 mm	2 Pcs.	15 Pcs.
	TG-MP-P-120-20-30-2	4260711991622	120x 20x 3,0 mm	2 Pcs.	10 Pcs.

Please note

The data in this technical data sheet are based on our current knowledge and experience. Due to the large amount of possible factors, this should not be construed as to release the users from doing their own tests and screening. No legally binding assurance of specific properties or applicability for a concrete purpose should be derived from these data. Please consider contacting us for further detail. It is the responsibility of the recipient of our products to ensure that any proprietary rights and existing laws and legislation are observed.

Trademark Information

Thermal Grizzly is a registered trademark.