

Heat-Shrink-Tube Reels 3:1


Item-No.: 24CA282 ... 24CA295, 25CA624 ... 25CA651



These high-quality shrink sleeves are particularly suitable for service workshops, electronics technicians and applications with a high demand for shrink tubing. The heat-shrink tube is wound onto a cardboard reel and can therefore be cut to length individually. Various available nominal diameters open up a wide range of applications. The version with inner glue and a shrink ratio of 3:1 is ideal for applications with high demands on the wrapping.

Technical Specifications

Material: PE • Shrink ratio: 3:1 • Hot melt adhesive • Shrink temperature (min.): 80 °C • Shrink temperature (max.): 125 °C • Operating temperature: -40 °C ... +125 °C • Tensile strength (min.): 10.4 MPa • Dielectric strength 15 kV/mm (30 s.) • Rated voltage: 600 V • Elongation break: min. 200% • Color: Black • Colors: Black, White, Transparent • Selling unit: Reel or per m.



Item-No.	Description	Diameter	Content	EAN/GTIN
24CA282	Shrinking tube with glue 3:1 black Φ 1.6 mm	1.6 mm	200 m	4260732287216
24CA283	Shrinking tube with glue 3:1 black Φ 2.4 mm	2.4 mm	200 m	4260732287223
24CA284	Shrinking tube with glue 3:1 black Φ 3.2 mm	3.2 mm	200 m	4260732287230
24CA285	Shrinking tube with glue 3:1 black Φ 4.8 mm	4.8 mm	100 m	4260732287247
24CA286	Shrinking tube with glue 3:1 black Φ 6.4 mm	6.4 mm	100 m	4260732287254
24CA287	Shrinking tube with glue 3:1 black Φ 7.9 mm	7.9 mm	100 m	4260732287261
24CA288	Shrinking tube with glue 3:1 black Φ 9.5 mm	9.5 mm	50 m	4260732287278
24CA289	Shrinking tube with glue 3:1 black Φ 12.7 mm	12.7 mm	50 m	4260732287285
24CA290	Shrinking tube with glue 3:1 black Φ 15.4 mm	15.4 mm	50 m	4260732287292
24CA291	Shrinking tube with glue 3:1 black Φ 19.1 mm	19.1 mm	50 m	4260732287308
24CA292	Shrinking tube with glue 3:1 black Φ 25.4 mm	25.4 mm	50 m	4260732287315
24CA293	Shrinking tube with glue 3:1 black Φ 30 mm	30 mm	25 m	4260732287322
24CA294	Shrinking tube with glue 3:1 black Φ 39 mm	39 mm	25 m	4260732287339
24CA295	Shrinking tube with glue 3:1 black Φ 50 mm	50 mm	25 m	4260732287346

Continue next page

Item-No.	Description	Diameter	Content	EAN/GTIN
25CA624	Shrinking tube with glue 3:1 white Φ 1.6 mm roll 200 m	1.6 mm	200 m	4262511622706
25CA625	Shrinking tube with glue 3:1 white Φ 2.4 mm roll 200 m	2.4 mm	200 m	4262511622713
25CA626	Shrinking tube with glue 3:1 white Φ 3.2 mm roll 200 m	3.2 mm	200 m	4262511622720
25CA627	Shrinking tube with glue 3:1 white Φ 4.8 mm roll 100 m	4.8 mm	100 m	4262511622737
25CA628	Shrinking tube with glue 3:1 white Φ 6.4 mm roll 100 m	6.4 mm	100 m	4262511622744
25CA629	Shrinking tube with glue 3:1 white Φ 7.9 mm roll 100 m	7.9 mm	100 m	4262511622751
25CA630	Shrinking tube with glue 3:1 white Φ 9.5 mm roll 50 m	9.5 mm	50 m	4262511622768
25CA631	Shrinking tube with glue 3:1 white Φ 12.7 mm roll 50 m	12.7 mm	50 m	4262511622775
25CA632	Shrinking tube with glue 3:1 white Φ 15.4 mm roll 50 m	15.4 mm	50 m	4262511622782
25CA633	Shrinking tube with glue 3:1 white Φ 19.1 mm roll 50 m	19.1 mm	50 m	4262511622799
25CA634	Shrinking tube with glue 3:1 white Φ 25.4 mm roll 50 m	25.4 mm	50 m	4262511622805
25CA635	Shrinking tube with glue 3:1 white Φ 30 mm roll 25 m	30 mm	25 m	4262511622812
25CA636	Shrinking tube with glue 3:1 white Φ 39 mm roll 25 m	39 mm	25 m	4262511622829
25CA637	Shrinking tube with glue 3:1 white Φ 50 mm roll 25 m	50 mm	25 m	4262511622836
25CA638	Shrinking tube with glue 3:1 transparent Φ 1.6 mm roll 200 m	1.6 mm	200 m	4262511622843
25CA639	Shrinking tube with glue 3:1 transparent Φ 2.4 mm roll 200 m	2.4 mm	200 m	4262511622850
25CA640	Shrinking tube with glue 3:1 transparent Φ 3.2 mm roll 200 m	3.2 mm	200 m	4262511622867
25CA641	Shrinking tube with glue 3:1 transparent Φ 4.8 mm roll 100 m	4.8 mm	100 m	4262511622874
25CA642	Shrinking tube with glue 3:1 transparent Φ 6.4 mm roll 100 m	6.4 mm	100 m	4262511622881
25CA643	Shrinking tube with glue 3:1 transparent Φ 7.9 mm roll 100 m	7.9 mm	100 m	4262511622898
25CA644	Shrinking tube with glue 3:1 transparent Φ 9.5 mm roll 50 m	9.5 mm	50 m	4262511622904
25CA645	Shrinking tube with glue 3:1 transparent Φ 12.7 mm roll 50 m	12.7 mm	50 m	4262511622911
25CA646	Shrinking tube with glue 3:1 transparent Φ 15.4 mm roll 50 m	15.4 mm	50 m	4262511622928
25CA647	Shrinking tube with glue 3:1 transparent Φ 19.1 mm roll 50 m	19.1 mm	50 m	4262511622935
25CA648	Shrinking tube with glue 3:1 transparent Φ 25.4 mm roll 50 m	25.4 mm	50 m	4262511622942
25CA649	Shrinking tube with glue 3:1 transparent Φ 30 mm roll 25 m	30 mm	25 m	4262511622959
25CA650	Shrinking tube with glue 3:1 transparent Φ 39 mm roll 25 m	39 mm	25 m	4262511622966
25CA651	Shrinking tube with glue 3:1 transparent Φ 50 mm roll 25 m	50 mm	25 m	4262511622973