



## K05WF50 & K05WF95 - HAND TOOLS FOR CRIMPING WIRE END FERRULES

Klauke Article Number: K05WF50, K05WF95

### **Short description**

Klauke Crimping Tool 25-50 mm<sup>2</sup>, 2x 16 mm<sup>2</sup> & 50 – 95 mm<sup>2</sup>

### **Scope of delivery**

- Klauke pressing tool in box



## Features

- **K05WF50** for crimping wire ferrules 25 - 50 mm<sup>2</sup> and twin ferrules 2 x 16 mm<sup>2</sup>
- **K05WF95** for crimping wire end ferrules 50 - 95 mm<sup>2</sup>
- **Easy operation** thanks to pre-clamping lever
- **Optimum fit** for connection in all standard plug-in and screw terminal blocks
- **High degree of compaction** due to square crimping
- **Increased press width** - reduces the number of presses required.
- Modern, dimensionally stable and lightweight elliptical handle tubes
- Effort-saving and fatigue-free tool mechanics
- Especially long-lasting

## Accessories

- Klauke Article Number: AE12550 crimping dies 25-50 mm<sup>2</sup>, 2x16 mm<sup>2</sup>
- Klauke Article Number: AE15095 crimping dies 50-95 mm<sup>2</sup>



## Product Data K05WF50

---

|                                            |                                              |
|--------------------------------------------|----------------------------------------------|
| International Product Number (GTIN) / EAN: | 4059577023369                                |
| UPC:                                       | -                                            |
| Klauke-Article Number:                     | K05WF50                                      |
| Special treatment class (dangerous goods): | No                                           |
| Keyword:                                   | mechanical crimping tool                     |
| Order Unit:                                | 1                                            |
| Content unit:                              | 1                                            |
| Packaging quantity:                        | 1                                            |
| Price unit:                                | 1                                            |
| Minimum quantity:                          | 1                                            |
| Gross weight:                              | 1,7 Kg                                       |
| Net weight:                                | 1,6 kg                                       |
| Dimensions (LxWxH):                        | 433x169x39 mm                                |
| Crimping range:                            | 25-50 mm <sup>2</sup> , 2x16 mm <sup>2</sup> |
| Customs tariff number:                     | 84672920                                     |
| Guarantee period:                          | 2 years                                      |
| Country of origin:                         | SK                                           |



## Product data K05WF95

---

|                                            |                          |
|--------------------------------------------|--------------------------|
| International Product Number (GTIN) / EAN: | 4059577023390            |
| UPC:                                       | -                        |
| Klauke-Article Number:                     | K05WF95                  |
| Special treatment class (dangerous goods): | No                       |
| Keyword:                                   | mechanical crimping tool |
| Order Unit:                                | 1                        |
| Content unit:                              | 1                        |
| Packaging quantity:                        | 1                        |
| Price unit:                                | 1                        |
| Minimum quantity:                          | 1                        |
| Gross weight:                              | 1,7 Kg                   |
| Net weight:                                | 1,6 kg                   |
| Dimensions (LxWxH):                        | 433x169x39 mm            |
| Crimping range:                            | 50-95 mm <sup>2</sup>    |
| Customs tariff number:                     | 82032000                 |
| Guarantee period:                          | 2 years                  |
| Country of origin:                         | SK                       |



## Product data AE12550

---

|                                            |                                                |
|--------------------------------------------|------------------------------------------------|
| International Product Number (GTIN) / EAN: | 4059577023406                                  |
| UPC:                                       | -                                              |
| Klauke-Article Number:                     | AE12550                                        |
| Special treatment class (dangerous goods): | No                                             |
| Keyword:                                   | crimping die                                   |
| Order Unit:                                | 1                                              |
| Content unit:                              | 1                                              |
| Packaging quantity:                        | 1                                              |
| Price unit:                                | 1                                              |
| Minimum quantity:                          | 1                                              |
| Gross weight:                              | 0.214 Kg                                       |
| Net weight:                                | 0,195 Kg                                       |
| Dimensions (LxWxH):                        | 60 x 24 x 40 mm                                |
| Crimping range:                            | 25 – 50 mm <sup>2</sup> , 2x16 mm <sup>2</sup> |
| Customs tariff number:                     | 82073010                                       |
| Guarantee period:                          | 2 years                                        |
| Country of origin:                         | ES                                             |



## Product data AE15095

---

|                                            |                         |
|--------------------------------------------|-------------------------|
| International Product Number (GTIN) / EAN: | 4059577023413           |
| UPC:                                       | -                       |
| Klauke-Article Number:                     | AE15095                 |
| Special treatment class (dangerous goods): | No                      |
| Keyword:                                   | crimping die            |
| Order Unit:                                | 1                       |
| Content unit:                              | 1                       |
| Packaging quantity:                        | 1                       |
| Price unit:                                | 1                       |
| Minimum quantity:                          | 1                       |
| Gross weight:                              | 0.214 Kg                |
| Net weight:                                | 0,195 Kg                |
| Dimensions (LxWxH):                        | 60 x 24 x 40 mm         |
| Crimping range:                            | 50 – 95 mm <sup>2</sup> |
| Customs tariff number:                     | 82073010                |
| Guarantee period:                          | 2 Jahre                 |
| Country of origin:                         | ES                      |