


Heat-Shrink-Tube Boxes 3:1 with Glue

Item-No.: 23CA172 ... 23CA183
25CA484 ... 25CA507
Black, White, Transparent



These high-quality heat-shrinking-tubes are particularly suitable for service workshops, electronics technicians and laboratory needs. In a carton dispenser box the black heat-shrink-tube (one per size) is stored and individually shortenable. Perfect results with hot-melt inner adhesive glue: waterproof when correctly overlapped and applied! The product can be used for insulation, protective covering of components, as anti-kink protection, anti-corrosion, as well as repair of cables and lines, and much more. High quality product from industrial applications!

Technical Specifications

Material: PE • Shrink temperature: 90 °C ... 125 °C • Operating temperature: -40 °C ... +125 °C • Tensile strength (min.): 10.4 MPa • Dielectric strength 15 kV/mm (30 sec.) • Flammability based on VW-1 • Rated voltage: 600 V • Shrink ratio: 3:1 • Volume resistivity: min. $10^{14} \Omega$ • Elongation break: min. 300%.

Versions

Item-No.	Description	Diameter	Color	Content	EAN/GTIN
23CA172	Shrinking-Tube Black $\varnothing$ 1.6 mm 3:1 w. Glue 10 m	1.6 mm	Black	10 m	4260732283812
23CA173	Shrinking-Tube Black $\varnothing$ 2.4 mm 3:1 w. Glue 10 m	2.4 mm	Black	10 m	4260732283829
23CA174	Shrinking-Tube Black $\varnothing$ 3.2 mm 3:1 w. Glue 10 m	3.2 mm	Black	10 m	4260732283836
23CA175	Shrinking-Tube Black $\varnothing$ 4.8 mm 3:1 w. Glue 5 m	4.8 mm	Black	5 m	4260732283843
23CA176	Shrinking-Tube Black $\varnothing$ 6.4 mm 3:1 w. Glue 5 m	6.4 mm	Black	5 m	4260732283850
23CA177	Shrinking-Tube Black $\varnothing$ 7.9 mm 3:1 w. Glue 5 m	7.9 mm	Black	5 m	4260732283867
23CA178	Shrinking-Tube Black $\varnothing$ 9.5 mm 3:1 w. Glue 5 m	9.5 mm	Black	5 m	4260732283874
23CA179	Shrinking-Tube Black $\varnothing$ 12.7 mm 3:1 w. Glue 5 m	12.7 mm	Black	5 m	4260732283881
23CA180	Shrinking-Tube Black $\varnothing$ 15 mm 3:1 w. Glue 5 m	15 mm	Black	5 m	4260732283898
23CA181	Shrinking-Tube Black $\varnothing$ 19.1 mm 3:1 w. Glue 5 m	19.1 mm	Black	5 m	4260732283904
23CA182	Shrinking-Tube Black $\varnothing$ 25.4 mm 3:1 w. Glue 5 m	25.4 mm	Black	5 m	4260732283911
23CA183	Shrinking-Tube Black $\varnothing$ 30 mm 3:1 w. Glue 5 m	30 mm	Black	5 m	4260732283928
25CA484	Shrinking-Tube White $\varnothing$ 1.6 mm 3:1 w. Glue 10 m	1.6 mm	White	10 m	4262511620771
25CA485	Shrinking-Tube White $\varnothing$ 2.4 mm 3:1 w. Glue 10 m	2.4 mm	White	10 m	4262511620788

Item-No.	Description	Diameter	Color	Content	EAN/GTIN
25CA486	Shrinking-Tube White $\varnothing$ 3.2 mm 3:1 w. Glue 10 m	3.2 mm	White	10 m	4262511620795
25CA487	Shrinking-Tube White $\varnothing$ 4.8 mm 3:1 w. Glue 5 m	4.8 mm	White	5 m	4262511620801
25CA488	Shrinking-Tube White $\varnothing$ 6.4 mm 3:1 w. Glue 5 m	6.4 mm	White	5 m	4262511620818
25CA489	Shrinking-Tube White $\varnothing$ 7.9 mm 3:1 w. Glue 5 m	7.9 mm	White	5 m	4262511620825
25CA490	Shrinking-Tube White $\varnothing$ 9.5 mm 3:1 w. Glue 5 m	9.5 mm	White	5 m	4262511620832
25CA491	Shrinking-Tube White $\varnothing$ 12.7 mm 3:1 w. Glue 5 m	12.7 mm	White	5 m	4262511620849
25CA492	Shrinking-Tube White $\varnothing$ 15 mm 3:1 w. Glue 5 m	15 mm	White	5 m	4262511620856
25CA493	Shrinking-Tube White $\varnothing$ 19.1 mm 3:1 w. Glue 5 m	19.1 mm	White	5 m	4262511620863
25CA494	Shrinking-Tube White $\varnothing$ 25.4 mm 3:1 w. Glue 5 m	25.4 mm	White	5 m	4262511620870
25CA495	Shrinking-Tube White $\varnothing$ 30 mm 3:1 w. Glue 5 m	30 mm	White	5 m	4262511620887
25CA496	Shrinking-Tube Transp. $\varnothing$ 1.6 mm 3:1 w. Glue 10 m	1.6 mm	Transparent	10 m	4262511620894
25CA497	Shrinking-Tube Transp. $\varnothing$ 2.4 mm 3:1 w. Glue 10 m	2.4 mm	Transparent	10 m	4262511620900
25CA498	Shrinking-Tube Transp. $\varnothing$ 3.2 mm 3:1 w. Glue 10 m	3.2 mm	Transparent	10 m	4262511620917
25CA499	Shrinking-Tube Transp. $\varnothing$ 4.8 mm 3:1 w. Glue 5 m	4.8 mm	Transparent	5 m	4262511620924
25CA500	Shrinking-Tube Transp. $\varnothing$ 6.4 mm 3:1 w. Glue 5 m	6.4 mm	Transparent	5 m	4262511620931
25CA501	Shrinking-Tube Transp. $\varnothing$ 7.9 mm 3:1 w. Glue 5 m	7.9 mm	Transparent	5 m	4262511620948
25CA502	Shrinking-Tube Transp. $\varnothing$ 9.5 mm 3:1 w. Glue 5 m	9.5 mm	Transparent	5 m	4262511620955
25CA503	Shrinking-Tube Transp. $\varnothing$ 12.7 mm 3:1 w. Glue 5 m	12.7 mm	Transparent	5 m	4262511620962
25CA504	Shrinking-Tube Transp. $\varnothing$ 15 mm 3:1 w. Glue 5 m	15 mm	Transparent	5 m	4262511620979
25CA505	Shrinking-Tube Transp. $\varnothing$ 19.1 mm 3:1 w. Glue 5 m	19.1 mm	Transparent	5 m	4262511620986
25CA506	Shrinking-Tube Transp. $\varnothing$ 25.4 mm 3:1 w. Glue 5 m	25.4 mm	Transparent	5 m	4262511620993
25CA507	Shrinking-Tube Transp. $\varnothing$ 30 mm 3:1 w. Glue 5 m	30 mm	Transparent	5 m	4262511621006

