


## Hook-and-Loop Cable-Tie Set 10 pcs. Item-No.: 25CA560 ... 25CA575



These polyamide hook and loop cable ties are easy to open and close again. They are ideal for many bundling and fixing tasks, e.g. for objects, cables, sports equipment, plants, curtains, tools and much more. The outstanding material properties of polyamide enable a wide range of applications in terms of environmental conditions. The material is dimensionally stable, robust and resistant to many liquids - as well as UV radiation. The set of 10 hook and loop cable ties with a width of 1.2 cm

is ideal for all demanding indoor and outdoor applications. The black design can be used unrestrictedly and inconspicuously in many areas. With eyelet on one side - ideal for forming loops

Part-No.	Description	Dimensions	Content	GTIN
25CA560	Hook&Loop Cable Tie-Set 12x100 mm 10 pcs.	100 mm x 12 mm	10 pcs	4262511621945
25CA561	Hook&Loop Cable Tie-Set 12x150 mm 10 pcs.	150 mm x 12 mm	10 pcs	4262511621952
25CA562	Hook&Loop Cable Tie-Set 12x200 mm 10 pcs.	200 mm x 12 mm	10 pcs	4262511621969
25CA563	Hook&Loop Cable Tie-Set 12x250 mm 10 pcs.	250 mm x 12 mm	10 pcs	4262511621976
25CA564	Hook&Loop Cable Tie-Set 12x300 mm 10 pcs.	300 mm x 12 mm	10 pcs	4262511621983
25CA565	Hook&Loop Cable Tie-Set 12x350 mm 10 pcs.	350 mm x 12 mm	10 pcs	4262511621990
25CA566	Hook&Loop Cable Tie-Set 12x400 mm 10 pcs.	400 mm x 12 mm	10 pcs	4262511622003
25CA567	Hook&Loop Cable Tie-Set 12 mm 5 Sizes 50 pcs.	100 mm x 12 mm 150 mm x 12 mm 200 mm x 12 mm 250 mm x 12 mm 300 mm x 12 mm	50 pcs (10/size)	4262511622010
25CA568	Hook&Loop Cable Tie-Set 20x100 mm 10 pcs.	100 mm x 20 mm	10 pcs	4262511622027
25CA569	Hook&Loop Cable Tie-Set 20x150 mm 10 pcs.	150 mm x 20 mm	10 pcs	4262511622034
25CA570	Hook&Loop Cable Tie-Set 20x200 mm 10 pcs.	200 mm x 20 mm	10 pcs	4262511622041
25CA571	Hook&Loop Cable Tie-Set 20x250 mm 10 pcs.	250 mm x 20 mm	10 pcs	4262511622058
25CA572	Hook&Loop Cable Tie-Set 20x300 mm 10 pcs.	300 mm x 20 mm	10 pcs	4262511622065
25CA573	Hook&Loop Cable Tie-Set 20x350 mm 10 pcs.	350 mm x 20 mm	10 pcs	4262511622072
25CA574	Hook&Loop Cable Tie-Set 20x400 mm 10 pcs.	400 mm x 20 mm	10 pcs	4262511622089
25CA575	Hook&Loop Cable Tie-Set 20mm 5 Sizes 50 pcs.	100 mm x 20 mm 150 mm x 20 mm 200 mm x 20 mm 250 mm x 20 mm 300 mm x 20 mm	50 pcs (10/size)	4262511622096

**Technical data:**  
Material: Polyamide •  
Temperature range: -20 ... 85 °C • Melting temperature: >250 °C • Color: black •  
RoHS compliant,  
REACH compliant.