

Trusted by Millions Now in Your Pool





ULTRAMARINE P1

Trusted by Millions Now in Your Pool



UltraPure Suction with 4800GPH Power

Thorough Cleaning, Effortlessly Achieved

The ULTRAMARINE P1 features groundbreaking 4800GPH UltraPure Suction Technology. Its high-performance motor and optimized S-flow anti-clog channel effortlessly lift debris from every surface, producing crystal-clear water. Equipped with four synchronized roller brushes and a dual-layer filter, it thoroughly scrubs pool floors and walls, capturing everything from large debris to fine particles. The result is pristine water with minimal effort.



10-tier Durability System

Built to Last, Cleans Without Limits

Powered by a 10-tier Durability System, the ULTRAMARINE P1 is engineered for lasting performance. It features a marine-grade shell and a corrosion-proof titanium-stainless steel core that protects against chemicals and wear. Critical electronics are fully sealed to IP68 standards, while intelligent navigation and an anti-jamming system prevent damage and optimize cleaning paths. This combination ensures the P1 delivers reliable cleaning, season after season.



SmartNavi Intelligent Path Optimization

Smart Navigation, Cleaning Without Pause

Equipped with an advanced IMU-core multi-sensor fusion navigation system, it continuously tracks its position and movement to map out the most efficient cleaning path. This eliminates random bumping and avoids wasted effort in redundant coverage, ensuring complete cleaning. The result is a faster, more thorough clean—for a smart and consistently effortless experience.



Smart App Control

Hassle-Free Pool Care, Fully Automated

The ULTRAMARINE P1 delivers a truly hassle-free cleaning experience. Personalize it with three modes, three efficiency levels, and flexible scheduling to effortlessly target floors, walls, or the entire pool. Its completely cordless, app-controlled design eliminates cable hassles and tangles for ultimate flexibility and effortless remote control.



ULTRAMARINE P1

Key Technologies

Performance

- 4 Roller Brushes
- Strong suction up to 18 m³/h
- Up to 3 hours working time

Intelligence

- S- and N-pattern cleaning path
- Automatic Parking
- Obstacle Crossing by auxiliary wheels

Convenience

- Cordless
- APP Control
- Adaptive to various pool types
- 3 Cleaning Mode based on needs

ID Pictures



Specification

ULTRAMARINE P1

SRP	549€
Pool Dimension (max.)	180m²
Navigation Sensors	IMU
Driving & Pump Motor	2 & 1
Path planning	S-Pattern (Floor), N-Pattern (Wall+Waterline)
Auto parking / Parking at Waterline	v / x
Suction Power (max.)	18 m³/h
Roller Brushes	4 (Front+Rear)
Cleaning Coverage	Floor, Walls, Waterline, Slope
Cleaning Mode	Auto, Floor, Weekly (Eco)
Runtime per Charge	Up to 3 Hours
Charging Time	4 Hours
Battery Capacity	4600 mAh
APP control (Remote Control)	v
Filter basket capacity / type	3.5 L / 180 µm
IP	IP68
Operating Temperature	6°C - 35°C
Dimension of Robot	466*394*235 mm
Weight	10 kg

What is in the box?

Robot (incl. Standard filter*1) (pcs)	1
Charging Adapter (pcs)	1
Retrieval Hook (pcs)	1
User Manual (pcs)	1