

Perun 3 Mini

Compact Brilliance

MAX OUTPUT	MAX OUTPUT	MAX RUNTIME	MAX THROW	MAX RUNTIME
				
WHITE LIGHT	RED LIGHT	WHITE LIGHT	WHITE LIGHT	RED LIGHT
1,250 lumens	45 lumens	10 days	155 meters	19 hours

*This information is for market reference only. Please DO NOT make it public.



BLACK



ORANGE

Perun 3 Mini

Compact Brilliance



MARKET APPLICATIONS

Work light & Household & Outdoors

UPC :


Perun 3 Mini 6977261690759

Perun 3 Mini (Orange) 6977261692418

Perun 3 Mini NW (HCRI) 6977261692401

DESCRIPTION

The Perun 3 Mini is a compact, high-lumen rechargeable right-angle light that combines white and red light options in a versatile, portable design. As an upgrade to the Perun 2 Mini, it delivers 14% more white light, reaching up to 1,250 lumens. The red light features low, high, and SOS modes, ideal for night vision and emergency use. An upgraded headband and headlamp bracket allow quick switching between handheld and headlamp use, supporting a wide range of applications—from professional use to outdoor activities and everyday tasks. The magnetic tail enables secure attachment to iron surfaces and supports convenient magnetic charging. A stainless steel pocket clip offers flexible carry options, and the upgraded stainless steel button improves both durability and tactile response, delivering a premium user experience across varied environments.



FEATURES

- **Compact and Powerful:** Delivers up to 1,250 lumens with a 155-meter beam distance, providing exceptional performance for mid-to-close-range illumination in a compact form factor.
- **Long-Lasting Runtime:** Powered by a 650 mAh rechargeable battery, the Perun 3 Mini offers up to 10 days of continuous use in Moonlight mode, minimizing the need for frequent recharging.
- **Dual Light Sources for Versatility:** Features 5 white light modes and 3 red light modes, making it adaptable for various scenarios. The red light is ideal for preserving night vision or serving as an emergency signal.
- **Upgraded Headband and Bracket:** The lightweight headband features breathable holes, anti-sweat strip, and reflective material for enhanced comfort and safety. The quick-detach bracket allows easy transitions between headlamp and handheld use.
- **Multi-Scene Adaptability:** Compact design paired with a stainless steel pocket clip, lanyard hole, and magnetic tail ensures easy carry and hands-free use, making it ideal for work, outdoor activities, home use, and more.
- **Refined Metal Button with Battery Indicator:** The durable stainless-steel button adds a premium tactile feel and improved durability. A laser micro-perforated tri-color power indicator provides instant, reliable battery status updates.

OUTPUT

White Light (Standard Version)					
SPECIFICATIONS	Turbo	High	Medium	Low	Moon
	1,250 $\pm$ 350 lumens	500 $\pm$ 350 lumens	100 lumens	10 lumens	2 lumens
	2+60 minutes	2+75 minutes	4.5 hours	30 hours	10 days
	155 meters	95 meters	45 meters	15 meters	5 meters
	6,000 cd	2,300 cd	500 cd	60 cd	7 cd

White Light (HCRI Version)					
SPECIFICATIONS	Turbo	High	Medium	Low	Moon
	920 $\pm$ 280 lumens	400 $\pm$ 280 lumens	85 lumens	10 lumens	2 lumens
	2+60 minutes	2+75 minutes	4.5 hours	30 hours	10 days
	133 meters	85 meters	41 meters	15 meters	5 meters
	4,416 cd	1,840 cd	425 cd	60 cd	7 cd

Red Light		
SPECIFICATIONS	High	Low
	45 lumens	5 lumens
	150 minutes	19 days
	10 meters	4 meters
	30 cd	4 cd

* **Note:** All data above are test results according to ANSI NEMA FL 1-2019 standards.

Perun 3 Mini

Compact Brilliance



LIGHT SOURCE

Standard Version:

High Performance Cool White LED and Red LED
(CCT: 5700K~6700K; CRI: 70)

HCRI Version:

High Performance Neutral White LED and Red LED
(CCT: 4000K~5000K; CRI: 90)

DIMENSIONS

Length: 2.53 in / 64.3 mm
Head Diameter: 0.87 in / 22 mm
Body Diameter: 0.81 in / 20.6 mm

WEIGHT

1.90 oz / 54 g (Including Battery)

BODY MATERIAL

Aluminum Alloy

POWERED BY

Customized 650 mAh 3.6 V 16340 Lithium-ion
Rechargeable Battery (included)

WARRANTY

Lifetime Warranty in Australia, China, France, Germany,
and the USA.

5-Year Warranty in Other Countries and Regions


Visit: <https://www.olight.com/lifetime-warranty>

IN THE BOX

Perun 3 Mini (Battery and Pocket Clip Included) x 1
MCC1A Magnetic Charging Cable x 1
Headband and Bracket x 1
User Manual x 1

WATERPROOF

IPX8



DROP TEST



COMPLIANCE



olight.com © OLIGHT 04/29/25 V1

Made in China

Note: There are slight differences between the picture and the real item caused by light color temperature. All the pictures are for reference only.