
DATASHEET


ESD Conductive PP Tweezers




Pointed tweezers

Item No.	3752509	3752515	3752506
Compliance	DIN EN 61340-5-1		
Tip shape	Pointed	Pointed	Pointed
Tip	0.2 mm straight	0.2 mm straight	1 mm straight
Tip length	11 mm	7 mm	35 mm
Dimensions (L x W)	120 x 10 mm	120 x 10 mm	120 x 10 mm
Weight	5 g	5 g	5 g
Material	PP		
Surface resistance	10^3 - 10^6 Ω		
Operating conditions	0 to +40 °C, 0 - 85 % RH (non-condensing)		
Storage conditions	-20 to +40 °C, 0 - 85 % RH (non-condensing)		
Delivery Content	1x tweezers		

Item no 3752509



Item no 3752515




Item no 3752506




Flat tweezers

Item No.	3752510	3752507	3752511
Compliance	DIN EN 61340-5-1		
Tip shape	Flat	Flat	Flat
Tip	6 mm straight	3 mm straight	6 mm straight
Tip length	12 mm	11 mm	12 mm
Dimensions (L x W)	120 x 10 mm	120 x 10 mm	120 x 10 mm
Weight	5 g	5 g	5 g
Material	PP		
Surface resistance	10^3 - 10^6 Ω		
Operating conditions	0 to +40 °C, 0 - 85 % RH (non-condensing)		
Storage conditions	-20 to +40 °C, 0 - 85 % RH (non-condensing)		
Delivery Content	1x tweezers		


Item no 3752510



Item no 3752507




Item no 3752511



Curved tweezers

Item No.	3752508
Compliance	DIN EN 61340-5-1
Tip shape	Curved
Tip	0.5 mm straight
Tip length	12.5 mm
Dimensions (L x W)	120 x 10 mm
Weight	5 g
Material	PP
Surface resistance	10^3 - 10^6 Ω
Operating conditions	0 to +40 °C, 0 - 85 % RH (non-condensing)
Storage conditions	-20 to +40 °C, 0 - 85 % RH (non-condensing)
Delivery Content	1x tweezers

Item no 3752508



This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92242 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright 2026 by Conrad Electronic SE.