

USB-C Docking Stations



		Office & Home					Travel
							
Article Number		DA-70914	DA-70915	DA-70917	DA-70918	DA-70919	DA-70916
Product Name		USB-C Docking Station, 7-Port	USB-C Docking Station, 8-Port	USB-C Docking Station, 11-Port	USB-C Docking Station, 13-Port	USB-C 8K Docking Station, 12-Port	USB-C Travel Docking Station, 7-Port
Number of Ports		7	8	11	13	12	7
Connection to Host		USB-C 3.2 Gen 2	USB-C 3.2 Gen 2	USB-C 3.2 Gen 2	USB-C 3.2 Gen 2	USB-C 3.2 Gen 2	USB-C 3.2 Gen 1
Video	Number of external Monitors	1	2	3	3	3	1
	HDMI Ports	1	2	2	3	2	1
	DisplayPort Ports	X	X	1	2	1	X
	Maximum Resolution	4K/60Hz	4K/60Hz	4K/60Hz	4K/60Hz	8K/30Hz	4K/60Hz
	OS Compatibility - MST Mode	X	Windows, ChromeOS, Linux	Windows, ChromeOS, Linux	Windows, macOS, ChromeOS, Linux	Windows, ChromeOS, Linux	X
USB Ports	USB-A 3.2 Gen 1 Ports	X	X	X	3	2	2
	USB-A 3.2 Gen 2 Ports	2	2	2	1	1	X
	USB-C Ports (Data)	X	X	1	1	1	X
Additional Ports	SD / MicroSD	✓	✓	✓	X	✓	✓
	Gigabit Ethernet Port	✓	✓	✓	✓	✓	✓
	Audio Port (3,5 mm)	X	X	✓	✓	✓	X
	Anti-Theft Protection	X	X	✓	✓	✓	X
Power Supply	USB-C Port (PD)	✓	✓	X	X	✓	✓
	Power Supply	100 Watt (85W Host, 15W Dock)	100 Watt (85W Host, 15W Dock)	150 Watt (100W Host, 50W Dock)	150 Watt (96W Host, 54W Dock)	100 Watt (85W Host, 15W Dock)	100 Watt (85W Host, 15W Dock)
	PD Version	3.0	3.0	X	X	3.0	3.0
	Charging Function for USB Devices	✓	✓	✓	✓	✓	✓
	DC Port	X	X	✓	✓	X	X
	Incl. Power Supply Unit	X	X	✓	✓	X	X
General Information	Housing	Aluminium / ABS plastic	Aluminium / ABS plastic	Aluminium / ABS plastic	Aluminium / ABS plastic	Aluminium / ABS plastic	Aluminium / ABS plastic
	Cable Length	20 cm	20 cm	100 cm	100 cm	20 cm	10 cm
	Color	Grey / Black	Grey / Black	Grey / Black	Grey / Black	Grey / Black	Grey / Black
	OS Compatibility in General	Windows, macOS, iOS, iPad, Android, ChromeOS, Linux					

All brand names and logos are trademarks or registered trademarks of their respective owners. Subject to technical changes, errors and design-related deviations from the illustrations. All information is provided without guarantee. We do not accept liability for printing errors. Delivery subject to availability. Publisher: ASSMANN Electronic GmbH, Auf dem Schüffel 3, 58513 Lüdenscheld, Germany. 07/2025