

Lenovo Multi-port USB-C 100W GaN Charger

Compact design. Unlimited potential.



Smarter
technology
for all

Lenovo

BLACK

SEASHELL



EU



EU



UK



UK



US



US

Overview

Wherever your day takes you— from studio sessions to café brainstorm — the Lenovo Multi-Port USB-C 100W GaN Charger keeps every device ready to go. With three USB-C ports in a compact, toss-and-travel design, it's the ultimate power hub that keeps your ideas flowing and your inspiration fully charged.

Key Features



Compact powerhouse

Advanced GaN technology lets this charger deliver uncompromising power in a travel-ready, ultra-compact design — ideal for young creatives on the move, studio work, or back-to-back trips.




Charge everything

Power up all your essentials at once—laptop, tablet, and phone—thanks to three versatile USB-C ports. Keep your entire ecosystem powered, synced, and ready for the next task.



Extreme performance

With single-port up to 100W fast charging, it powers your laptop at full speed—without throttling or overheating. Works in harmony with your PC to ensure smooth performance, all in a travel-smart design that replaces bulky chargers and keeps you productive anywhere.



Smarter
technology
for all

Lenovo

Specification

Performance

CONNECTIVITY

3 x USB-C Ports

AC INPUT

90V-264V

DC OUTPUT

USB-C 1 / USB-C 2	: 100W (Max.)
USB-C 3	: 22.5W (Max.) (SCP)
Dual USB-C Ports Usage	: 65W + 30W
All Ports Usage	: 65W + 20W + 10W

CHARGING INDICATOR

LED

ADAPTER TYPE

Wall Mount

FOLDABLE PLUGS

Yes (for US/JP pin only)

MULTI-PLUG

US / UK / EU Plug PNs

Design

DIMENSION (W x D x H)

(mm)	: 70 x 30.5 x 70
(inches)	: 2.76" x 1.20" x 2.76"

COLORS

Black
Seashell

CABLE

In the Box, Detachable Braided 1.8 m USB-C Cable

Information

PART NUMBER (PN) SKUs

Commercial Black

US	: 40AW100BUS
UK	: 40AW100BUK
EU	: 40AW100BEU

Consumer Black

US	: GOA6100BUS
UK	: GOA6100BUK
EU	: GOA6100BEU

Seashell

US	: GOA6100SUS
UK	: GOA6100SUK
EU	: GOA6100SEU

WARRANTY

1 Year Limited Warranty

SHIP GROUP (WHAT'S IN THE BOX)

Lenovo Multi-port USB-C 100W GaN Charger
1.8 m USB-C Braided Cable
Warranty Card
User Guidance

BLACK



SEASHELL



accessorysmartfind.lenovo.com

Lenovo reserves the right to alter product offerings and specifications at any time, without notice. Lenovo makes every effort to ensure accuracy of all information but is not liable or responsible for any editorial, photographic, or typographic errors. All images are for illustration purposes only. For full Lenovo product, service, and warranty specifications, visit www.lenovo.com. Lenovo makes no representations or warranties regarding third-party products or services. **Trademarks:** The following are trademarks or registered trademarks of Lenovo: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkServer, ThinkVantage, and ThinkVision. Other company, product, and service names may be trademarks or service marks of others. Battery life (and recharge times) will vary based on many factors, including system settings and usage. Visit www.lenovo.com/lenovo/us/en/safecomp/ periodically for the latest information on safe and effective computing. ©2026 Lenovo. All rights reserved.

Smarter
technology
for all

Lenovo