

Lenovo
YOGA

Lenovo Yoga Creative Keyboard AngryMiao Edition

Where every keystroke unleashes brilliance.



Smarter
technology
for all

Lenovo

Overview

A premium co-developed keyboard designed for young creatives who value both tactile precision and typing experience. Built with multi-layer structure and refined switch design, it delivers a controlled, immersive typing experience while enabling intuitive creative control through customizable inputs and seamless ecosystem integration.

Target Audience

Young Creatives

Key Features



Refined sound, tuned by design

With our 8-layer gasket system, this structure refines every typing sound, delivering a clean, tailored acoustic profile. Every keystroke offers a dynamic typing feel, keeping you locked into creativity flow.




One knob, dedicated control

Engineered for creative workflows, the control knob makes adjustments more intuitive — each tactile step guiding users frame by frame through video edits. A switch supports up to three knob behaviors, adapting to different needs.



Tactile elegance, high-speed logic

Refined and bold—an effortless extension of Yoga aesthetics. This design harmonizes tactile finishes with the high-speed logic of dual USB-C connectivity, ensuring an elegance, clutter-free workspace.



Lenovo

Specification

Performance

CONNECTIVITY

Wired

POLLING RATE

1000 Hz

KEYBOARD CONFIGURATIONS

Keyboard Layout : US English
Front Height : 18.8 mm
Typing Angle : 8°
Mount : Gasket
Switching Mounting Style : Hot-swappable

OPERATING TEMPERATURE

Maximum : 50° C (122° F)
Minimum : 0° C (32° F)

RELATIVE HUMIDITY

Maximum : 90%
Minimum : 10%

USB PORTS

Upstream Port : 1 x USB-C 3.1 Gen 1*, To System
Downstream Port : 2 x USB-C 3.1 Gen 1*, 5Gbps, 5V/0.9A

MAX. WATTAGE

4.5W + 4.5W

Design

DIMENSIONS (W x D x H)

(mm) : 413 x 144 x 52
(in) : 16.26 x 5.67 x 2.05

WEIGHT

Starting at 2499.6 g (5.51 lbs)

LIGHTING

Key Backlighting / Star Ring Lighting

Information

SUPPORTED OS

Windows / MacOS

WARRANTY

1 Year

SHIPMENT GROUP (WHAT'S IN THE BOX)

Yoga Creative Keyboard AngryMiao Edition
USB-C to USB-C Cable
Information Posters
Quick Start Guide



accessorysmartfind.lenovo.com

Lenovo reserves the right to alter product offerings and specifications at any time, without notice. Lenovo makes every effort to ensure accuracy of all information but is not liable or responsible for any editorial, photographic, or typographic errors. All images are for illustration purposes only. For full Lenovo product, service, and warranty specifications, visit www.lenovo.com. Lenovo makes no representations or warranties regarding third-party products or services. **Trademarks:** The following are trademarks or registered trademarks of Lenovo: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkServer, ThinkVantage, and ThinkVision. Other company, product, and service names may be trademarks or service marks of others. Battery life (and recharge times) will vary based on many factors, including system settings and usage. Visit www.lenovo.com/lenovo/us/en/safecomp/ periodically for the latest information on safe and effective computing. ©2026 Lenovo. All rights reserved.

Smarter
technology
for all

Lenovo