
BRUMBERG
Light. Since 1873.

PEPA Flat 48 V track, length: 3,000 mm
Article no. 88487380





IP20 48 V

Tender
Flat 48 V track, length: 3,000 mm, black, Rectangular. Compact design for harmonious implementation in well-rounded architectural room concepts. Mounting method: Surface mounting, Place of installation: Ceiling-/Wall-/Pendant-mounted, Material: Aluminium, Degree of protection: (DIN EN 60529) IP20, Protection class: (DIN EN 61140) III, Voltage: 48 V DC, .


All technical data as well as, weight and measurements are based on rated values and had been carefully prepared. We reserve the right to make technical changes which are are important in progressing. Product pictures are examples and can vary from the original. Subject to errors.
Date 12.08.2026 Orders are placed under our general terms and conditions under https://www.brumberg.com/en/terms-and-conditions/general-terms-and-conditions-of-sale/

BRUMBERG
Light. Since 1873.

PEPA Flat 48 V track, length: 3,000 mm

Article no. 88487380

Leistung	maximale Schienenlänge in Metern
100 Watt	50 m
250 Watt	35 m
Angabe beziehen sich auf eine Last, die der gelieferten Leistung entspricht und gleichmäßig auf die entsprechende Länge in der Tabelle verteilt ist.	



Article data	
Article no.	88487380
GTIN	4255752520177
Series name	PEPA
Short description	Flat 48 V track, length: 3,000 mm
Material	Aluminium
Colour	black
RAL colour	9005
Type of surface	Structure
Shape	Rectangular
Length	3,000 mm
Width	26.2 mm
Hight	21 mm
Weight	2.1 kg
stamp	ENEC
Conformance	CE, UKCA

Operating technology of the luminaire	
Voltage type	DC
DC nominal voltage min	48 V
DC nominal voltage max	48 V
Protection class	III
Degree of protection	IP20
Wire number	4

All technical data as well as, weight and measurements are based on rated values and had been carefully prepared. We reserve the right to make technical changes which are are important in progressing. Product pictures are examples and can vary from the original. Subject to errors.
Date 12.08.2026 Orders are placed under our general terms and conditions under https://www.brumberg.com/en/terms-and-conditions/general-terms-and-conditions-of-sale/

BRUMBERG
Light. Since 1873.

PEPA Flat 48 V track, length: 3,000 mm

Article no. 88487380

Operating technology of driver	
DC nominal voltage min	48 V
DC nominal voltage max	48 V
Protection class	III
Degree of protection	IP20
Nominal cross-section	2.00 mm2

Mounting technology	
Mounting method	Surface mounting
Place of installation	Ceiling-/Wall-/Pendant-mounted

Packing data	
Gross weight	2.12 kg
Length of packaging	3,002 mm
Packaging width	26 mm
Packaging hight	22 mm
Disposal at end of life	This product must not be disposed of with household waste. You are obliged, to dispose of such electrical waste separately. By disposing of electrical waste and other old or defective electronics separately, you support recycling or other forms of re-use. In that way you help to take care and to avoid that harmful substances get into the environment.

All technical data as well as, weight and measurements are based on rated values and had been carefully prepared. We reserve the right to make technical changes which are are important in progressing. Product pictures are examples and can vary from the original. Subject to errors.
Date 12.08.2026 Orders are placed under our general terms and conditions under https://www.brumberg.com/en/terms-and-conditions/general-terms-and-conditions-of-sale/

BRUMBERG
Light. Since 1873.

PEPA Flat 48 V track, length: 3,000 mm
Article no. 88487380

Optional accessories
Article no.: 88482080 End piece for 48 V track DALI / without cable hole Dimensions: 26.4 mm x 21 mm x 2.5 mm https://www.brumberg.com/fileadmin/products/Datenblatt_88482080_2021_DE.pdf
Article no.: 88482180 End cap for flat 48 V DALI track / with cable outlet Dimensions: 26.4 mm x 21 mm x 2.5 mm https://www.brumberg.com/fileadmin/products/Datenblatt_88482180_2021_DE.pdf
Article no.: 88484080 L-connector 90° to 48 V track Dimensions: 105 mm x 16.3 mm x 18.2 mm https://www.brumberg.com/fileadmin/products/Datenblatt_88484080_2021_DE.pdf
Article no.: 88484180 Flexible connector for 48 V track Dimensions: 273.5 mm x 16.3 mm x 18.2 mm https://www.brumberg.com/fileadmin/products/Datenblatt_88484180_2021_DE.pdf
Article no.: 88484280 Final power supply to 48 V track Dimensions: 111.7 mm x 16.3 mm x 18.2 mm https://www.brumberg.com/fileadmin/products/Datenblatt_88484280_2021_DE.pdf
Article no.: 88484380 Electrical connector for 48 V track Dimensions: 105 mm x 16.3 mm x 18.2 mm https://www.brumberg.com/fileadmin/products/Datenblatt_88484380_2021_DE.pdf
Article no.: 17480100 LED converter for 48 V track system; the DALI signal is looped through and must be supplied separately Power: 1 - 100 W Dimensions: 298 mm x 16 mm x 19 mm https://www.brumberg.com/fileadmin/products/Datenblatt_17480100_2021_DE.pdf
Article no.: 17480200 LED converter for 48 V track system; the DALI signal is looped through and must be supplied separately Power: 1 - 250 W Dimensions: 268 mm x 22 mm x 43.5 mm https://www.brumberg.com/fileadmin/products/Datenblatt_17480200_2021_DE.pdf
Article no.: 81107000 Track pliers https://www.brumberg.com/fileadmin/products/Datenblatt_81107000_2021_DE.pdf
Article no.: 88488700 Cable suspension with quick release for flat 48 V track. Dimensions: 35 mm x 26.2 mm x 1.3 mm x 10.4 mm https://www.brumberg.com/fileadmin/products/Datenblatt_88488700_2021_DE.pdf

All technical data as well as, weight and measurements are based on rated values and had been carefully prepared. We reserve the right to make technical changes which are are important in progressing. Product pictures are examples and can vary from the original. Subject to errors.
Date 12.08.2026 Orders are placed under our general terms and conditions under https://www.brumberg.com/en/terms-and-conditions/general-terms-and-conditions-of-sale/

BRUMBERG
Light. Since 1873.

PEPA Flat 48 V track, length: 3,000 mm
Article no. 88487380

Optional accessories
Article no.: 88488730 Cable suspension with quick release for flat 48 V track. Dimensions: 35 mm x 26.2 mm x 1.3 mm x 10.4 mm https://www.brumberg.com/fileadmin/products/Datenblatt_88488730_2021_DE.pdf
Article no.: 88488750 Cable suspension with quick release for flat 48 V track. Dimensions: 35 mm x 26.2 mm x 1.3 mm x 10.4 mm https://www.brumberg.com/fileadmin/products/Datenblatt_88488750_2021_DE.pdf

All technical data as well as, weight and measurements are based on rated values and had been carefully prepared. We reserve the right to make technical changes which are are important in progressing. Product pictures are examples and can vary from the original. Subject to errors.
Date 12.08.2026 Orders are placed under our general terms and conditions under https://www.brumberg.com/en/terms-and-conditions/general-terms-and-conditions-of-sale/